

ABB BALDOR RELIANCE III

Customer information packet

ECS101T3K2P2EF4

2.2KW, 1500RPM, 3PH, 50HZ, D112S, 3624B, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	D112S
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Brushless Wound Field PM Rotor
Output @ Frequency	2.200 KW @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	380.0 V @ 50 HZ
Agency Approvals	WEEE UKCA CULUS CE BLUETOOTH
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	5
Current @ Voltage	4.400 A @ 380.0 V
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Frame Prefix	D
Heater Indicator	No Heater
High Voltage Full Load Amps	4.4 a

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGA0025
Layout	36LYT272
Eff. date	01-21-2025
CD Diagram	CD0006B03
Poles	04
Leads	3#16 19" LONG LEADS
Proprietary	False
Created date	02-14-2023


Insulation Class	F
Inverter Code	Inverter Duty
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Motor Type	3624B
Mounting Arrangement	B3
Number of Poles	4
Overall Length	16.34 IN
Power Factor	96
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.103 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1500 rpm
Speed Code	Single Speed
Starting Method	INVERTER SPECIAL
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate


NP3978A01						
PART NO.	ECIN4A5P8					
U1	400	PH	3	HZ	50	
I1	4.6	W/EXT. CHOKE				4.3
SERIAL #						

NP3968B01A01


CAT.NO.	ECS101T3K2P2EF4									
SPEC.	36-0000-3655				YR					
FRAME	D112S		IP		55	WT.		84		
KW	2.2	HZ		50	PH		3	DUTY-IPM		CONT
INS CL	F	CLASS RISE				AMB-C		40		
EFF. CL	IE5	EFF		91.9	COS0		96			
VOLTS	380			FLA		4.4				
1/MIN	1500			1/MIN MAX				3000		
BEMF (V)	177			RS (OHMS)				3.68		
LD (MH)	51			LQ (MH)				177		
VPWM	CP =		50	TO		100				
CT	5	TO		50	VT		1	TO		100
MATCHED INV	ECIN4A5P8									
DE	6206			ODE		6205				
SERIAL #										



36CB3503A00



MATERIAL: RAMPF, RAKU-PUR 32-3280-51L



SECTION A-A

REV. DESC: NEW

REV: -

VERSION: 00

REVISED: 09:13:16 01/15/2020

TDR: 000001129989



MODEL NO. 36CB3503A00

REF: -

BY: ENMARS0

Material: -

BALDOR - RELIANCE®

36 & 37 FRAME TOP ECM ALUMINUM COVER WITH FOAM SEAL

36CB3503A00

