

**BALDOR • RELIANCE**

---

# Customer information packet

## ECS101M0H5EB4

5HP, 1800RPM, 3PH, 60HZ, 184TC, TEFC, NONE

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	184TC
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
XP Class and Group	None
XP Division	Not Applicable
Agency Approvals	UL WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	10.500 A @ 230.0 V 5.300 A @ 460.0 V
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a
Insulation Class	F
Inverter Code	Inverter Duty

## Part detail



Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGA0020
Layout	36LYT262
Eff. date	05-08-2024
CD Diagram	CD0005A25
Poles	04
Leads	9#12
Proprietary	False
Created date	09-18-2020

IP Rating	NONE
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3632B
Mounting Arrangement	F1
Number of Poles	4
Overall Length	16.54 IN
Power Factor	97
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.50
Shaft Diameter	1.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1800 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

<b>NP3968A01A01</b>									
<b>CAT.NO.</b>	ECS101M0H5EB4								
<b>SPEC.</b>	36-0000-0419								
<b>FRAME</b>	184TC		<b>ENCL.</b>	TEFC	<b>IP</b>	54			
<b>HP</b>	5	40	<b>C AMB</b>		<b>CONT</b>				
<b>NOM. EFF.</b>	93.7	<b>PF</b>	97	<b>SF</b>	1.5				
<b>VOLTS</b>	230/460		<b>FLA</b>	10.5/5.3					
<b>RPM</b>	1800		<b>RPM-MAX</b>	4000					
<b>HZ</b>	60	<b>PH.</b>	3	<b>CLASS</b>	F				
<b>BEMF (V)</b>	126/252		<b>RS (OHMS)</b>	0.82/3.30					
<b>LD (MH)</b>	13.5/54.0		<b>LQ (MH)</b>	47.8/191.0					
<b>VPWM</b>	<b>CHP</b>	60	<b>TO</b>	133					
<b>CT</b>	6	<b>TO</b>	60	<b>VT</b>	1	<b>TO</b>	133		
<b>MATCHED INV</b>	ACS380-04XX-[N/A]/07A2-4								
<b>DE</b>	6206		<b>ODE</b>	6205					
<b>SERIAL #</b>									

36LYT262



REV. DESC: UPDATE DRAWING GRAPHICS

REV: B	VERSION: 02	REVISED: 01:28:51 03/16/2022	TDR: 000001187699
--------	-------------	------------------------------	-------------------



MODEL NO. 36LYT262

REF: -

BY: ENJEFD0




Material: -

**BALDOR**

HOR 182-4TC TEFC B EYEBOLT INT SH GND ECS

36LYT262

CD0005A25



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005A25

REV. DESC: NEW		
REV. LTR: -	VERSION: 00	TDR: 000001135746
FILE: \AAA\00253\082	REVISED: 01:10:57 03/30/2020	BY: ENMARSO
MTL: -	© □	

**BALDOR - RELIANCE®**

3PH, DV, 9 LEADS, ECS  
SH 1 of 1