ABB BALDOR RELIANCE

Customer information packet

ECTM3664T-5G

2HP, 1165RPM, 3PH, 60HZ, 184T, 0642M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 1:24:00 AM

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.500 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	2.5 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	06J518
Base	
Status	PRD/A
Elec. spec.	06WGX236
Layout	06LYJ518
Eff. date	06-08-2023
CD Diagram	CD0006
Poles	06
Leads	3#16
Proprietary	False
Created date	04-20-2022

Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0642M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.93 IN
Power Factor	68
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260									
CAT.NO.	ECTM3664T-5G								
SPEC.	06J518X236G1								
HP	2								
VOLTS	575								
AMP	2.5								
RPM	1165								
FRAME	184T	**HZ**	60		**PH**	3			
SER.F.	1.15	**CODE**	K	**DES**	B	**CL**	F		
NEMA-NOM-EFF	88.5	**PF**	68						
RATING	40C AMB-CONT								
CC									
DE	6206	**ODE**	6205						
ENCL	TEFC	**SN**							
	INV DUTY 20:1 VT								

AC Induction Motor Performance Data
Record # 32952
Typical performance - not guaranteed values

Winding: 06WGX236-R001	**Type:** 0642M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			2	**Full Load Torque**	9 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			2.5	**Breakdown Torque**	31.3 LB-FT
R.P.M.			1165	**Pull-up Torque**	16.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	19.9 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	16.7 A
Service Factor (S.F.)			1.15	**No-load Current**	1.47 A
NEMA Nom. Eff.	88.5	**Power Factor**	68	**Line-line Res. @ 25ºC**	8.09 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	27°C
S.F. Amps				**Temp. Rise @ S.F. Load**	32°C
				Locked-rotor Power Factor	29
				Rotor inertia	0.395 LB-FT2

Load Characteristics 575 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	30	48	60	68	73	75	71
Efficiency	80.5	87.2	88.5	88.7	87.7	86.6	88.1
Speed	1193	1186	1178	1170	1161	1150	1165
Line amperes	1.57	1.8	2.13	2.5	2.94	3.45	2.76


ABB Motors and Mechanical Inc.


WINDING # 06WGX236

2 HP 3 PH 60 HZ 1165 RPM 575 V 0642M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=31.3 PU=16.7 LR=19.9 LRA=16.7





06LYJ518
(614-643) = 15.93
7.67
2.81
2.75
.25 KEY
1.75 LONG
.38-16 TAP
1.00 DEEP
(EACH END)
Ø 1.1250
1.1245
DOME
SLINGER
SLINGER
PLUG
8 HOLES
Ø.41
FRAME GRND
.25-20 TAP
4.50
.49
4.50
2.75
5.50
6.50
3 DRAIN FITTINGS
(EACH END)
12.23
7.18
5.05
2.02
9.25
4.50
4.44
LEAD HOLE
.75 N.P.T.
.125 N.P.T.
DRAIN PLUG
(1 EA. SIDE)
3.75
3.75
5.82
4.39
8.78
V-RING
SLINGER
LIP SEAL
INTERNAL
SHAFT GROUND
PULLEY END DETAIL
CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP
AND VERTICAL SHAFT DOWN LIFTING; REMOVE EYEBOLT
FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW FOR CCT STOCK DEVELOPMENT
REV: - VERSION: 00 REVISED: 03:31:40 04/22/2022 TDR: 000001187869
MODEL NO. 06LYJ518 REF: -
BY: ENSTEK0 B
BALDOR - RELIANCE®
HOR 182-4T TEFC CP COOLING TOWER, SLD BRGS, SEALS, AEGIS INT
06LYJ518


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1