ABB BALDOR RELIANCE

Customer information packet

ECTM3768T-G

5HP, 1160RPM, 3PH, 60HZ, 15T, 0746M, TEFC, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 11:39:36 AM

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CURUSEEV
	NEMA PREMIUM
	NEMA_PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.400 A @ 460.0 V
	15.300 A @ 208.0 V
	14.800 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	B
Type	AC
Mech. spec.	07D718
Base	
Status	PRD/A
Elec. spec.	07WGY763
Layout	07LYD718
Eff. date	06-08-2023
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	04-20-2022

Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	7.4 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0746M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.58 IN
Power Factor	71
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1160 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260									
CAT.NO.	ECTM3768T-G								
SPEC.	07D718Y763G1								
HP	5								
VOLTS	230/460								
AMP	14.8/7.4								
RPM	1160								
FRAME	215T	**HZ**	60		**PH**	3			
SER.F.	1.15	**CODE**	K	**DES**	A	**CL**	F		
NEMA-NOM-EFF	89.5	**PF**	71						
RATING	40C AMB-CONT								
CC									
DE	6307	**ODE**	6206						
ENCL	TEFC	**SN**							
	INV DUTY 20:1 VT								

AC Induction Motor Performance Data
Record # 50558
Typical performance - not guaranteed values

Winding: 07WGY763-R005	**Type:** 0746M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	22.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			14.8/7.4	**Breakdown Torque**	81.3 LB-FT
R.P.M.			1160	**Pull-up Torque**	49.9 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	59.9 LB-FT
NEMA Design Code	A	**KVA Code**	K	**Starting Current**	54.8 A
Service Factor (S.F.)			1.15	**No-load Current**	4.03 A
NEMA Nom. Eff.	89.5	**Power Factor**	71	**Line-line Res. @ 25ºC**	1.64 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	50°C
S.F. Amps				**Temp. Rise @ S.F. Load**	61°C
				Locked-rotor Power Factor	22.2
				Rotor inertia	1.14 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	32	51	63	70	74	76	72
Efficiency	84.9	89.7	90.6	90.4	89.2	87.7	89.7
Speed	1190	1181	1174	1164	1153	1141	1157
Line amperes	4.32	5.06	6.12	7.48	8.92	10.5	8.34


ABB Motors and Mechanical Inc.


WINDING # 07WGY763

5 HP 3 PH 60 HZ 1160 RPM 460 V 0746M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=81.3 PU=49.9 LR=59.9 LRA=54.8




07LYD718
(717-750) = 19.58
9.20
3.88
3.38
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
.38-16 TAP
1.12 DEEP
(EACH END)
DOME SLINGER
3 DRAIN FITTINGS
(EA. END)
PLUG
SLINGER
FRAME GRND
.25-20 TAP
8 HOLES
.41 DIA.
5.50
.57
5.50
3.50
7.00
8.13
15.59
9.50
6.10
2.05
10.98
5.25
5.19
LEAD HOLE
1.00 N.P.T.
.125 N.P.T.
DRAIN PLUG
(EACH SIDE)
4.25
4.25
7.44
4.92
9.83
LIP SEAL
(EACH END)
V-RING
SLINGER
INTERNAL
SHAFT GROUND
6206
6307
FRONT END DETAIL
PULLEY END DETAIL
CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP
AND VERTICAL SHAFT DOWN LIFTING, REMOVE EYEBOLT
FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD ODE SEAL DETAIL
REV: A
VERSION: 01
REVISED: 03:15:45 05/02/2025
TDR: 000001255378
MODEL NO. 07LYD718
REF: -
BY: USTRTAY1
B
BALDOR
HOR 213-5T TEFC CP COOLING TOWER, SLD BRGS, SEALS, AEGIS INT
07LYD718

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS