

**BALDOR • RELIANCE**

---

# Customer information packet

## ECTM2276T-5G

7.5HP, 1180RPM, 3PH, 60HZ, 254T, 0954M, TEFC, F

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.700 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	Tapped & Key
Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	8.7 a
Insulation Class	F

## Part detail

Revision	G
Type	AC
Mech. spec.	09N188
Base	
Status	PRD/A
Elec. spec.	09WGT170
Layout	09LYN188
Eff. date	11-20-2023
CD Diagram	CD0006
Poles	06
Leads	3#12
Proprietary	False
Created date	04-12-2022

Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0954M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	23.55 IN
Power Factor	70
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

---

<b>NP1260</b>									
<b>CAT.NO.</b>	ECTM2276T-5G								
<b>SPEC.</b>	09N188T170G1								
<b>HP</b>	7.5								
<b>VOLTS</b>	575								
<b>AMP</b>	8.7								
<b>RPM</b>	1180								
<b>FRAME</b>	254T	<b>HZ</b>	60	<b>PH</b>	3				
<b>SER.F.</b>	1.15	<b>CODE</b>	J	<b>DES</b>	A	<b>CL</b>	F		
<b>NEMA-NOM-EFF</b>	91	<b>PF</b>	70						
<b>RATING</b>	40C AMB-CONT								
<b>CC</b>									
<b>DE</b>	6309	<b>ODE</b>	6208						
<b>ENCL</b>	TEFC	<b>SN</b>							
	INV DUTY 20:1 VT								

---

**AC Induction Motor Performance Data**

Record # 49111

Typical performance - not guaranteed values

Winding: 09WGT170-R001		Type: 0954M	Enclosure: TEFC		
<b>Nameplate Data</b>			<b>575 V, 60 Hz: Single Voltage Motor</b>		
Rated Output (HP)	7.5	Full Load Torque	33.1 LB-FT		
Volts	575	Start Configuration	direct on line		
Full Load Amps	8.7	Breakdown Torque	109 LB-FT		
R.P.M.	1180	Pull-up Torque	40 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque	55.6 LB-FT
NEMA Design Code	A	KVA Code	J	Starting Current	58 A
Service Factor (S.F.)	1.15	No-load Current	4.69 A		
NEMA Nom. Eff.	91	Power Factor	70	Line-line Res. @ 25°C	1.47 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	36°C	
S.F. Amps			Temp. Rise @ S.F. Load	43°C	
			Locked-rotor Power Factor	25.9	
			Rotor inertia	4.34 lb-ft <sup>2</sup>	

**Load Characteristics 575 V, 60 Hz, 7.5 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	53	64	70	74	76	72
Efficiency	83.4	89	91	91.1	90.6	89.8	90.8
Speed	1196	1192	1188	1183	1178	1172	1180
Line amperes	5.05	5.95	7.17	8.71	10.4	12.4	9.72


ABB Motors and Mechanical Inc.

WINDING # 09WGT170


Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1180 RPM 575 V 0954M

TORQUES (LB-FT): PO=109 PU=40 LR=55.6 LRA=58



12/2/2024 ACPERF, record # 49111



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

**BALDOR - RELIANCE®**

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1