

ABB BALDOR RELIANCE III

Customer information packet

ECTM2332T-G-AO

10 AIR OVERHP, 1180RPM, 3PH, 60HZ, 256T, 0960

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	256T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	30.000 A @ 208.0 V 28.200 A @ 230.0 V 14.100 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	G
Type	AC
Mech. spec.	09N187
Base	
Status	PRD/A
Elec. spec.	09WGT193
Layout	09LYN187
Eff. date	02-19-2024
CD Diagram	CD0005
Poles	06
Leads	9#12
Proprietary	False
Created date	03-25-2022

Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	14.1 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0960M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	23.09 IN
Power Factor	72
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2178									
CAT.NO.	ECTM2332T-G-AO								
SPEC.	09N187T193G1								
HP	10 AIR OVER								
VOLTS	230/460								
AMP	28.2/14.1								
RPM	1180								
FRAME	256T	HZ		60	PH		3		
SER.F.	1.15	CODE	H	DES	B	CL	F		
NEMA-NOM-EFF	91	PF	72						
RATING	40C AMB-CONT								
CC									
DE	6309	ODE		6208					
ENCL	TEAO	SN							
	INV DUT 20:1 VT								

AC Induction Motor Performance Data

Record # 52109

Typical performance - not guaranteed values

Winding: 09WGT193-R004			Type: 0960M		Enclosure: TEAO		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10 AIR OVER	Full Load Torque		44.3 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		28.2/14.1	Breakdown Torque		121 LB-FT		
R.P.M.		1180	Pull-up Torque		50.6 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque		67 LB-FT		
NEMA Design Code		B	KVA Code		H	Starting Current	81 A
Service Factor (S.F.)		1.15	No-load Current		6.84 A		
NEMA Nom. Eff.		91	Power Factor		72	Line-line Res. @ 25°C	0.746 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		38°C		
S.F. Amps			Temp. Rise @ S.F. Load		46°C		
			Locked-rotor Power Factor		24.9		
			Rotor inertia		4.82 LB-FT2		

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	36	57	67	72	74	75	73
Efficiency	85.8	90.7	91.9	91.7	91.1	89.4	91.3
Speed	1195	1191	1186	1181	1174	1166	1177
Line amperes	7.45	9.13	11.4	14.1	17.3	21.1	16

ABB Motors and Mechanical Inc.

WINDING # 09WGT193

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1180 RPM 460 V 0960M

TORQUES (LB-FT): PO=121 PU=50.6 LR=67 LRA=81





