ABB BALDOR RELIANCE

Customer information packet

ECTM4104T-5G

30HP, 1770RPM, 3PH, 60HZ, 286T, 1056M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 11:30:47 AM

Specifications

Enclosure	TEFC
Frame	286T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	Tapped & Key
Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	29.0 a
Insulation Class	F

Part Detail

Revision	G
Type	AC
Mech. spec.	10T010
Base	
Status	PRD/A
Elec. spec.	10WGY759
Layout	10LYT010
Eff. date	11-03-2025
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	04-14-2022

Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.57 IN
Power Factor	83
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260								
CAT.NO.	ECTM4104T-5G							
SPEC.	10T010Y759G1							
HP	30							
VOLTS	575							
AMP	29							
RPM	1770							
FRAME	286T	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	G	**DES**	A	**CL**	F	
NEMA-NOM-EFF	93.6	**PF**	83					
RATING	40C AMB-CONT							
CC	010A							
DE	6311	**ODE**	6309					
ENCL	TEFC	**SN**						
	INV DUTY 20:1VT							

AC Induction Motor Performance Data
Record # 30991
Typical performance - not guaranteed values

Winding: 10WGY759-R001	**Type:** 1056M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			30	**Full Load Torque**	89.2 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			29	**Breakdown Torque**	255 LB-FT
R.P.M.			1770	**Pull-up Torque**	120 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	136 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	177 A
Service Factor (S.F.)			1.15	**No-load Current**	11.5 A
NEMA Nom. Eff.	93.6	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.375 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	71°C
				Locked-rotor Power Factor	32
				Rotor inertia	4.45 LB-FT2

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	47	69	77	84	84	83	84
Efficiency	90.9	93.9	94.4	94	92.9	92.5	93.4
Speed	1794	1786	1780	1773	1764	1754	1768
Line amperes	13.3	17.6	23.4	28.5	35.9	43.6	32.9


ABB Motors and Mechanical Inc.


WINDING # 10WGY759

30 HP 3 PH 60 HZ 1770 RPM 575 V 1056M

TORQUES(LB-FT): PO=255 PU=120 LR=136 LRA=177


Typical performance - not guaranteed values.





10LYT010
(1030 - 1076) = 27.57
12.69
4.75
4.63
PLUG
DOME SLINGER
.50 KEY 3.25 LONG
PLUG
Ø 1.875 1.874
.50-13 TAP 1.25 DEEP (EACH END)
3 DRAIN FITTINGS (EACH END)
V-RING SLINGER
FRAME GRND .25-20 TAP
DRAIN PLUG (EACH SIDE) (REF)
9.50
9.50
.92
11.00
4.75
8 HOLES Ø.53
12.84
15.72
12.63
7.81
2.70
14.44
7.00 6.94
LEAD HOLE 1.50 NPT
.125 NPT DRAIN PLUG (EACH SIDE)
5.50
5.50
10.25
6.38
12.75
LIP SEAL
V-RING SLINGER
INTERNAL SHAFT GROUND
PULLEY END DETAIL
CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP AND VERTICAL SHAFT DOWN LIFTING, REMOVE EYEBOLT FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW FOR CCT STOCK DEVELOPMENT
REV: - VERSION: 00 REVISED: 04:53:46 04/25/2022 TDR: 000001185763
MODEL NO. 10LYT010 REF: -
BY: USODDIL B
BALDOR - RELIANCE®
HOR TEFC 284-6T CP COOLING TOWER,LIFT,SLD BRGS,SEAL PU,AEGIS
10LYT010


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1