ABB BALDOR RELIANCE

Customer information packet

ECTM4308T-G

40HP, 1190RPM, 3PH, 60HZ, 364T, A36062M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 6:56:59 AM

Specifications

Enclosure	TEFC
Frame	364T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	107.000 A @ 208.0 V
	49.800 A @ 460.0 V
	99.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	49.8 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 4 AWG

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG1194
Layout	617438-196
Eff. date	06-06-2023
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	04-07-2022

Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.78 IN
Power Factor	80
Product Family	Cooling Tower
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.374 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

000613007EW												
CAT.NO.	ECTM4308T-G			**SPEC NO.**	A36-7949-1194							
HP	40HP	**AMPS**	99.6/49.8		**VOLTS**	230/460			**DESIGN**	B		
FRAME	364T	**RPM**	1190		**HZ**	60	**AMB**	40	**SF**	1.15		
DRIVE END BEARING	65BC03JGG30A		**PH**	3	**DUTY**	CONT		**INSUL.CLASS**		F		
OPP D.E. BEARING	65BC03JGG30A		**TYPE**	P	**ENCL**	TEFC	**CODE**	G				
D.E.BRG.DATA	6313			**POWER FACTOR**	80				**NEMA NOM EFFICIENCY**	94.1		
O.D.E.BRG.DATA	6313			**MAX CORR KVAR**	12.00				**GUARANTEED EFFICIENCY**	93		
3/4 LOAD EFF.	94.1			**NEMA NOM/CSA QUOTED EFF**								
SER.NO.				**MOTOR WEIGHT**								

000901002AAA
INV DUTY 20:1 VT

AC induction motor performance data

Record #93159 - Typical performance - not guaranteed values

Winding	A36WG1194
Type	A3662M
Enclosure	TEFC

Nameplate data			
Rated Output			40
Volts			230/460
Full Load Amps			99.6/49.8
R.P.M.			1190
Hz	60	Phase	3
KVA Code			G
S.F.			1.15
NEMA Nom. Eff.	94.1	Power Factor	80
Duty			CONT
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection	
Full Load Torque	176.8 LB-FT
Start Configuration	direct on line
Breakdown Torque	514 LB-FT
Pull-up Torque	266 LB-FT
Locked-rotor Torque	335 LB-FT
Starting Current	312 A
No-load Current	18.7
Line-line Res. @ 25°C	0.14922 Ω
Temp. Rise @ Rated Load	43°C
Temp. Rise @ S.F. Load	51°C
Locked-rotor Power Factor	25.4
Rotor inertia	0

Load Characteristics 460 V, 60 Hz, 40 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	5	46	67	77	80	82	82	81
Efficiency	0	90	93.5	94.2	94.1	93.7	93	93.9
Speed	1199	1195.3	1193	1190.2	1187.5	1184.3	1181.4	1186
Line amperes	18.7	22.4	29.7	38.9	49.3	60.9	73.7	56.3

ABB BALDOR RELIANCE


REVIEW

CUSTOMER INFORMATION PACKET ECTM4308T-G - 40HP, 1190RPM, 3PH, 60HZ, 364T, A36062M, TEFC

WINDING # A36WG1194

40 HP 3 PH 60 HZ 1190 RPM 460 V A3662M

TORQUES(LB-FT): PO=514.00 PU=266.00 LR=335.00 LRA=312.00



USBRRAN1 6/12/2023 ACPERF, record # 93159

SHEET NUMBER 1 OF 1

617438-196

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1 SIDE

FRAME 365T

INCLUDES 364T FRAME MOUNTING HOLES

COOLING: FAN COOLED



CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP AND VERTICAL SHAFT DOWN LIFTING, REMOVE EYEBOLT FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY. MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

DIMENSIONS ARE IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE TEFC NOTE			
REV: A	VERSION: 01	REVISED: 01:11:28 07/27/2026	TDR: 000001281709
MODEL NO. 617438-196			
BY: USDOSCO2			C

BALDOR


E365T TEFC FT- F1- SLGR, SPCL DRAIN, VERT LIFTING, SH GND


617438-196

617438-196

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002