






609141-100

- NOTES:
- SHAFT STANDARDS PER 3425
 - X/P SURFACE PER DWG. 402111-A
 - BARSTOCK WEIGHT: 62 LBS

TOLERANCE UNLESS OTHERWISE SHOWN:	
ONE PLACE DECIMAL	±0.1
TWO PLACE DECIMAL	±0.02
THREE PLACE DECIMAL	±0.003
ANGLE	±0°-30'
SURFACE FINISH	250



1	CORE KEY	34180-070	GA	FS CLI	50 LBS
1	FINISHED SHAFT	3.12 X 28.71	A		
RA	NAME	SIZE OR CASTING	SYM	46024-	WT. (LB.)

BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE
AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED
OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

REV. DESC: NEW SHAFT

REV: -

VERSION: 00

REVISED: 08:00:19 12/01/2015

TDR: 000000936515

MODEL NO. 609141-100

REF:

BY: USBRSPI

Material: FSCLI

B

BALDOR

SHAFT E365T 6313-6313 TENV FINISH TURN

609141-100