

ABB BALDOR RELIANCE III

Customer information packet

ECTM3665T

5 AIR OVERHP, 1750RPM, 3PH, 60HZ, 184T, 0642M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEAO
Frame	184T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.600 A @ 460.0 V 14.000 A @ 208.0 V 13.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	H
Type	AC
Mech. spec.	06K700
Base	
Status	PRD/A
Elec. spec.	06WGX182
Layout	06LYK700
Eff. date	06-06-2024
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	08-14-2015

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.68 IN
Power Factor	79
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2134									
CAT.NO.	ECTM3665T								
SPEC.	06K700X182G1								
HP	5 AIR OVER								
VOLTS	208-230/460								
AMP	14-13.2/6.6								
RPM	1750								
FRAME	184T		HZ	60		PH		3	
SER.F.	1.15		CODE	J	DES	B		CL	F
NEMA-NOM-EFF	89.5		PF	79					
RATING	40C AMB-CONT								
CC									
DE	6206		ODE	6205					
ENCL	TEAO		SN						

AC Induction Motor Performance Data

Record # 35543

Typical performance - not guaranteed values

Winding: 06WGX182-R003			Type: 0642M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		5 AIR OVER		Full Load Torque		15 LB-FT	
Volts		208-230/460		Start Configuration		direct on line	
Full Load Amps		14-13.2/6.6		Breakdown Torque		53.9 LB-FT	
R.P.M.		1750		Pull-up Torque		22.4 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		31.8 LB-FT	
NEMA Design Code		B	KVA Code	J	Starting Current		46.6 A
Service Factor (S.F.)		1.15		No-load Current		3.02 A	
NEMA Nom. Eff.		89.5	Power Factor	79	Line-line Res. @ 25°C		2.63 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
				Locked-rotor Power Factor		40.5	
				Rotor inertia		0.391 LB-FT2	

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	41	63	75	81	84	85	81
Efficiency	85.2	89.8	90.4	89.8	88.4	86.9	88.6
Speed	1789	1777	1765	1752	1737	1721	1739
Line amperes	3.35	4.14	5.21	6.45	7.91	9.47	7.52


ABB Motors and Mechanical Inc.


WINDING # 06WGX182

Typical performance - not guaranteed values.



5 HP 3 PH 60 HZ 1750 RPM 460 V 0642M

TORQUES (LB-FT): PO=53.9 PU=22.4 LR=31.8 LRA=46.6





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005