ABB BALDOR RELIANCE

Customer information packet

ECTM3764T-5G

3HP, 1165RPM, 3PH, 60HZ, 213T, 0736M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 11:44:36 AM

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.600 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	3.6 a
Insulation Class	F


Part Detail

Revision	B
Type	AC
Mech. spec.	07D718
Base	
Status	PRD/A
Elec. spec.	07WGY849
Layout	07LYD718
Eff. date	06-08-2023
CD Diagram	CD0006
Poles	06
Leads	3#14
Proprietary	False
Created date	04-20-2022

Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.58 IN
Power Factor	71
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None


Nameplate


NP1260								
CAT.NO.	ECTM3764T-5G							
SPEC.	07D718Y849G1							
HP	3							
VOLTS	575							
AMP	3.6							
RPM	1165							
FRAME	213T	**HZ**	60		**PH**	3		
SER.F.	1.15	**CODE**	K	**DES**	B	**CL**	F	
NEMA-NOM-EFF	89.5	**PF**	71					
RATING	40C AMB-CONT							
CC								
DE	6307	**ODE**	6206					
ENCL	TEFC	**SN**						
	INV DUTY 20:1 VT							


07LYD718
(717-750) = 19.58
9.20
3.88
3.38
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
.38-16 TAP
1.12 DEEP
(EACH END)
DOME SLINGER
3 DRAIN FITTINGS
(EA. END)
PLUG
SLINGER
FRAME GRND
.25-20 TAP
8 HOLES
.41 DIA.
5.50
.57
5.50
3.50
7.00
8.13
15.59
9.50
6.10
2.05
10.98
5.25
5.19
LEAD HOLE
1.00 N.P.T.
.125 N.P.T.
DRAIN PLUG
(EACH SIDE)
4.25
4.25
7.44
4.92
9.83
LIP SEAL
(EACH END)
V-RING
SLINGER
INTERNAL
SHAFT GROUND
6206
6307
FRONT END DETAIL
PULLEY END DETAIL
CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP
AND VERTICAL SHAFT DOWN LIFTING, REMOVE EYEBOLT
FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD ODE SEAL DETAIL
REV: A
VERSION: 01
REVISED: 03:15:45 05/02/2025
TDR: 000001255378
MODEL NO. 07LYD718
REF: -
BY: USTRTAY1
B
BALDOR
HOR 213-5T TEFC CP COOLING TOWER, SLD BRGS, SEALS, AEGIS INT
07LYD718


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1