

ABB BALDOR RELIANCE III

Customer information packet

EFM2535T

30HP, 1775RPM, 3PH, 60HZ, 286T, 4060M, OPSB, F2

Specifications

Enclosure	OPSB
Frame	286T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	74.000 A @ 230.0 V 77.000 A @ 208.0 V 37.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	37.0 a

Part Detail

Revision	N
Type	AC
Mech. spec.	40E402
Base	
Status	PRD/A
Elec. spec.	40WGX339
Layout	40LYE402
Eff. date	09-15-2025
CD Diagram	CD0005
Poles	04
Leads	9#10
Proprietary	False
Created date	06-10-2016

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4060M
Mounting Arrangement	F2
Number of Poles	4
Overall Length	26.06 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138L																	
CAT.NO.	EFM2535T				P/N						ENCLOSURE		OPSB				
SPEC.	40E402X339			CC	010A		FRAME		286T		S/N						
HP	30				CLASS		F		HZ		60						
RPM	1775				PH	3		DES		A							
VOLT	230/460								KVA-CODE		H		ODE BRG		6309	DE BRG	6311
AMP	74/37																
RATING	40C AMB-CONT				GREASE		POLYREX EM										
NEMA-NOM-EFF	94.1	PF	80	SER.F.		1.15											
HTR-VOLTS			HTR-AMPS														

Accessories

Part number	Description	Multiplier
40-1400	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 56978

Typical performance - not guaranteed values

Winding: 40WGX339-R001			Type: 4060M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		30	Full Load Torque		88.8 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		72/36	Breakdown Torque		280 LB-FT		
R.P.M.		1775	Pull-up Torque		130 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		161 LB-FT	
NEMA Design Code		A	KVA Code	H	Starting Current		252 A
Service Factor (S.F.)		1.15	No-load Current		15.4 A		
NEMA Nom. Eff.		94.1	Power Factor	82	Line-line Res. @ 25°C		0.22043 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		29°C
S.F. Amps					Temp. Rise @ S.F. Load		35°C
					Locked-rotor Power Factor		31.4

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	44	67	77	82	85	85	84
Efficiency	90.5	93.8	94.4	94.3	93.9	93.2	94.1
Speed	1793.6	1788.1	1782.5	1776.9	1770.4	1763.1	1773
Line amperes	17.7	22.5	29	36.3	44.3	53	41.1

ABB Motors and Mechanical Inc.

WINDING # 40WGX339

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1775 RPM 460 V 4060M

TORQUES (LB-FT): PO=280 PU=130 LR=161 LRA=252





