

ABB BALDOR RELIANCE III

Customer information packet

EFM4312T

50HP, 1185RPM, 3PH, 60HZ, 365T, A3668M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	124.000 A @ 230.0 V 132.000 A @ 208.0 V 62.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	62.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs

Part Detail

Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4262
Layout	617428-078
Eff. date	07-08-2024
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	09-30-2022

Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3668M
Mounting Arrangement	F2
Number of Poles	6
Overall Length	33.49 IN
Power Factor	81
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate
NP3979LUA

CAT #		EFM4312T				SER				CC		010A															
SPEC		A36-8069-4262				RATING		40C AMB-CONT																			
HZ		VOLTS		AMPS		RPM		HP		CODE		SF		DES		PF		NEMA NOM. EFF									
60		230		124/62		1185		50		G		1.15		B		81 %		94.1 %									
		-														% %		% %									
PH		3		CL F		MAX CORR KVAR		15.8																			
BRG		DE		6313		ODE		6313		ENCL		TEFC		FR		365T		54									
GREASE		POLYREX EM												MTR WT		908		LBS									
USABLE AT		50HZ 40HP 190/380V 120/60A												SF1.0													
INVERTER DUTY		CT		15-60		HZ		4:1		VT		3-60		HZ		20:1		CHP		60-90		HZ		1.5:1		1.0 SF VPWM	
MAX RPM		1800		SFA 142/71																							

ABB BALDOR RELIANCE III S/O		CUSTOMER INFORMATION PACKET				
FRAME		HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
365HP		50	P	3/60	1185	230/460
AMPS	DUTY	AMB °C/ INSUL	S.F.	NEMA DESIGN	CODE LETTER	ENCLOSURE
124/61.9	CONT	40/F	1.15	B	G	TEFC
E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)		
-	418141089AE	---	---	.0290/.116		
PERFORMANCE						
LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY	
NO LOAD	0	23.9	1200	5.00	0	
1/4	12.5	28.4	1197	45.8	90.1	
2/4	25.0	37.2	1194	67.2	93.6	
3/4	37.5	48.7	1191	76.4	94.3	
4/4	50.0	61.9	1188	80.3	94.2	
5/4	62.5	76.1	1185	82.0	93.7	
SPEED TORQUE						
		RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES	
LOCKED ROTOR		0	165	365	375	
PULL UP		540	147	325	335	
BREAKDOWN		1135	253	559	200	
FULL LOAD		1188	100	221	61.9	
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.						
TYPICAL DATA NEMA NOM. EFF. 94.1 PCT						
		DRAWN BY: <u>C.B.ATANGANE</u> CHECKED BY: <u>J. P. TSAO</u> APPROVED BY: <u>W. L. SMITH</u> DATE: <u>11/12/25</u>		AC MOTOR PERFORMANCE DATA		A36WG4262-R001
						DATE ISSUED 11/12/25

FRAME 365HP

HP 50

TYPE	P
------	---

PHASE / HERTZ 3/60

CUSTOMER INFORMATION PACKET

R INFORMATIC
REV 1182**VOLTS 230/460**

AMPS 124/61.9

DUTY CONT

AMB °C / INSUL 40/F

EFM4312T - 50HP, 1185RPM, 3PH, 60HZ, 265T, A3668M, TEFC, F

S.F. 1.15

NEMA DESIGN B

CODE LETTER G

ENCLOSURE TEFC

E/S -


Z, 265T, A3668M, TEEG, F
ROTOR 418141089, AF

TEST S.O. TYPICAL DATA

TEST DATE --

STATOR RES. @ 25°C .0290/.116

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 230/460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.




DRAWN BY: C.B.ATANGANE
CHECKED BY: J. P. TSAO
APPROVED BY: W. L. SMITH
DATE: 11/12/25

AC MOTOR PERFORMANCE DATA



A36WG4262-R001

ISSUE DATE 11/12/25



416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED



(N.P. 1575-B)

REV. DESC: FONT CHANGE FOR PDF SEARCHABLE		
REV. LTR: A	VERSION: 01	TDR: 000001009382
FILE: \MGA\00000\661	REVISED: 02:46:19 02/13/2020	BY: MGHMTT
MTL: —		

BALDOR - RELIANCE®

CONN DIAG — STANDARD 9 LEAD, DELTA-CONNECTED
SH 1 of 1

416820-002