

DUTY MASTER ALTERNATING CURRENT MOTORS
SQUIRREL-CAGE INDUCTION





617429-011

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F2

G405T/G404T FRAME MOUNTING HOLES

COOLING: FAN COOLED



1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

2 GROUND TAPS QTY (1) 1/2-13 TAP; QTY (1) 3/8-16 TAP

DIMENSIONS ARE IN INCHES.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
WEIGHT (LBS): 1350, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE MODEL TO ADD EXT HARDWARE NO CHG TO PRINT			
REV: C	VERSION: 03	REVISED: 09:48:33 07/08/2022	TDR: 000001193529
MODEL NO. 617429-011		REF:	
BY: USBUFRA		Material:	

BALDOR

G405/404T TEFC F2 FOOT/STEEL CONDUIT BOX

C

SHEET NUMBER
1 OF 2

617429-011

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

617429-011

DUTY MASTER ALTERNATING CURRENT MOTORS
SQUIRREL-CAGE INDUCTION





617429-011

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F2

G405T/G404T FRAME MOUNTING HOLES

COOLING: FAN COOLED



DIMENSIONS ARE IN MILLIMETERS.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
WEIGHT (KG): 612. MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

2 GROUND TAPS QTY (1) 1/2-13 TAP; QTY (1) 3/8-16 TAP

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

SHEET NUMBER
2 OF 2

617429-011

REV. DESC: UPDATE MODEL TO ADD EXT HARDWARE NO CHG TO PRINT			
REV: C	VERSION: 03	REVISED: 09:48:33 07/08/2022	TDR: 000001193529
MODEL NO. 617429-011		REF:	
BY: USBUFRA		Material:	

BALDOR

G405/404T TEFC F2 FOOT/STEEL CONDUIT BOX

C

617429-011