ABB BALDOR RELIANCE

Customer information packet

EHM2535T-8

30HP, 1770RPM, 3PH, 60HZ, 286T, 4052M, OPSB, F1

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 5:36:40 AM

Specifications

Enclosure	OPSB
Frame	286T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	81.000 A @ 200.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	81.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs

Part Detail

Revision	V
Type	AC
Mech. spec.	40J098
Base	
Status	PRD/A
Elec. spec.	40WGW491
Layout	40LYJ098
Eff. date	04-25-2025
CD Diagram	CD0006
Poles	04
Leads	3#6
Proprietary	False
Created date	10-22-2010

Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4052M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	25.06 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2094E06B03									
CAT.NO.	EHM2535T-8								
SPEC.	40J098W491G1								
HP	30								
VOLTS	200								
AMPS	81								
RPM	1770								
FRAME	286T	**HZ**	60	**PH**	3				
SER.F.	1.15	**CODE**	G	**DES**	B	**CL**	F		
NEMA-NOM-EFF	94.1	**PF**	85						
RATING	40C AMB-CONT								
CC	010A	**USABLE AT 208V**		N/A					
DE	6311	**ODE**	6309						
AUTO		**MANUAL**		**NONE**					
ENCL	OPSB	**SN**							
BLANK									

AC Induction Motor Performance Data
Record # 16453
Typical performance - not guaranteed values

Winding: 40WGW491-R001	**Type:** 4052M	**Enclosure:** OPSB

Nameplate Data				**200 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			30	**Full Load Torque**	88.9 LB-FT
Volts			200	**Start Configuration**	direct on line
Full Load Amps			81	**Breakdown Torque**	272 LB-FT
R.P.M.			1770	**Pull-up Torque**	127 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	149 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	514 A
Service Factor (S.F.)			1.15	**No-load Current**	30.6 A
NEMA Nom. Eff.	94.1	**Power Factor**	85	**Line-line Res. @ 25ºC**	0.0423 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	31°C
S.F. Amps				**Temp. Rise @ S.F. Load**	40°C
				Locked-rotor Power Factor	32
				Rotor inertia	4.13 LB-FT2

Load Characteristics 200 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	50	72	82	85	87	87	86
Efficiency	90.3	93.6	94.2	94.1	93.6	92.7	93.8
Speed	1792	1785	1777	1769	1761	1752	1764
Line amperes	35.7	47.7	63	80.3	99	119.8	91.3


ABB Motors and Mechanical Inc.


WINDING # 40WGW491

30 HP 3 PH 60 HZ 1770 RPM 200 V 4052M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=272 PU=127 LR=149 LRA=514





40LYJ098
(4024-4046) = 23.81
(4048-4056) = 25.06
(4058-4064) = 26.06
4.78
4.94
4.63
.50 KEY
3.25 LONG
Ø1.875
1.874
Ø2.50
(REF)
6 HOLES
Ø.53
9.50
.63
11.00
4.75
12.25
13.40
12.21
6.70
LIFT LUG
(EA END)
50°
2.132
50°
3 HOLES
5-40 TAP
THRU ON
Ø2.783 B.C.
W/SCREWS
13.62
7.00 +.00 -.06
2 HOLES
6-32 TAP
THRU
Ø2.783 B.C.
W/SCREWS
LEAD HOLE
Ø2.50
5.50
5.50
9.71
6.13
12.25
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: FIX LIFTING LUG GRAPHICS
REV: M
VERSION: 11
REVISED: 10:51:55 01/15/2026
TDR: 000001270293
MODEL NO. 40LYJ098
REF: -
BY: USJOCUR5
B
BALDOR
HORZ OPSB 284-6T, HVAC MOTOR W/DUAL SH GND MTG
40LYJ098


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1