

ABB BALDOR RELIANCE III

Customer information packet

EHFM3157T

2HP, 1750RPM, 3PH, 60HZ, 145T, 3526M, OPSB, F2

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.900 A @ 460.0 V 5.800 A @ 208.0 V 5.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	N
Type	AC
Mech. spec.	35VV803
Base	
Status	PRD/A
Elec. spec.	35WGM496
Layout	35LYVV803
Eff. date	01-14-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-26-2013

High Voltage Full Load Amps	2.9 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524M
Mounting Arrangement	F2
Number of Poles	4
Overall Length	11.62 IN
Power Factor	76
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP2094E06B03											
CAT.NO.	EHFM3157T										
SPEC.	35VV803M496G1										
HP	2										
VOLTS	230/460										
AMPS	5.8/2.9										
RPM	1750										
FRAME	145T		HZ	60				PH	3		
SER.F.	1.15	CODE	K		DES	B		CL	F		
NEMA-NOM-EFF	86.5		PF	76							
RATING	40C AMB-CONT										
CC	010A				USABLE AT 208V			N/A			
DE	6205		ODE	6203							
AUTO	N		MANUAL		N		NONE	Y			
ENCL	OPSB	SN									
BLANK	SFA 6.3/3.2										

AC Induction Motor Performance Data

Record # 33882

Typical performance - not guaranteed values

Winding: 35WGM496-R001			Type: 3528M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		2	Full Load Torque		6.02 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		5.8/2.9	Breakdown Torque		22.6 LB-FT		
R.P.M.		1750	Pull-up Torque		11.27 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		15.4 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		21.65 A
Service Factor (S.F.)		1.15	No-load Current		1.63 A		
NEMA Nom. Eff.		86.5	Power Factor	76	Line-line Res. @ 25°C		8.22 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		38°C
S.F. Amps					Temp. Rise @ S.F. Load		45°C
					Locked-rotor Power Factor		59.1
					Rotor inertia		0.154 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	35	56	69	76	81	84	79
Efficiency	77	84.7	86.8	86.6	85.8	84.3	86.1
Speed	1789	1779	1768	1756	1742	1727	1748
Line amperes	1.75	2.01	2.37	2.85	3.37	3.96	3.16

ABB Motors and Mechanical Inc.

WINDING # 35WGM496

Typical performance - not guaranteed values.

2 HP 3 PH 60 HZ 1750 RPM 460 V 3528M

TORQUES (LB-FT) : PO=22.6 PU=11.27 LR=15.4 LRA=21.65





