ABB BALDOR RELIANCE

Customer information packet

EJMM2513T-G

15HP, 1765RPM, 3PH, 60HZ, 254JM, 3948M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/9/2026 2:39:42 PM

Specifications

Enclosure	OPSB
Frame	254JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.000 A @ 460.0 V
	36.000 A @ 230.0 V
	38.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	18.0 a
Insulation Class	H

Part Detail

Revision	R
Type	AC
Mech. spec.	39E447
Base	
Status	PRD/A
Elec. spec.	39WGY375
Layout	39LYE447
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	04
Leads	9#12
Proprietary	False
Created date	09-29-2017

Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3948M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	24.69 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	EJMM2513T-G								
SPEC.	39E447Y375G1								
HP	15								
VOLTS	230/460								
AMPS	36.4/18.2								
RPM	1770								
FRAME	254JM	**HZ**	60		**PH**	3			
SF	1.15	**CODE**	J	**DES**	A	**CLASS**	H		
NEMA NOM. EFF	93	**PF**	83						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	**SN**							
DE	6309	**ODE**	6208						
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 15HP 190/380V 42/21A								SF1.0

AC Induction Motor Performance Data
Record # 67094
Typical performance - not guaranteed values

Winding: 39WGY375-R002	**Type:** 3948M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	44.53 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			36/18	**Breakdown Torque**	141 LB-FT
R.P.M.			1765	**Pull-up Torque**	60.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	77.2 LB-FT
NEMA Design Code	A	**KVA Code**	G	**Starting Current**	117 A
Service Factor (S.F.)			1.15	**No-load Current**	6.37 A
NEMA Nom. Eff.	93	**Power Factor**	85	**Line-line Res. @ 25ºC**	0.62591 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	26°C
S.F. Amps				**Temp. Rise @ S.F. Load**	32°C
				Locked-rotor Power Factor	32.8

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	51	73	81	85	87	87	86
Efficiency	89.9	93.1	93.5	93	92.3	91.2	92.6
Speed	1792	1784.7	1776.9	1768	1759.3	1748.7	1763
Line amperes	7.67	10.4	13.8	17.7	21.8	26.5	20.2


ABB Motors and Mechanical Inc.


WINDING # 39WGY375

15 HP 3 PH 60 HZ 1765 RPM 460 V 3948M


TORQUES(LB-FT): PO=141 PU=60.4 LR=77.2 LRA=117


Typical performance - not guaranteed values.





39LYE447
3920 - 3944 = 23.19
3946 - 3956 = 24.69
3958 - 3964 = 25.69
5.250
CHECK W/GAUGE T-9041
3.000±.015
.625±.015
.25
3.91
UNDERCUT R.054-.043
.250 KEYWAY
2.62 LONG
(ENDMILLED)
.25 KEY
2.00 LONG
NAMEPLATE
Ø 8.500
8.497
Ø 1.2495
1.2490
Ø 1.3750
1.3745
Ø 1.750
1.748
.50-13 R.H
CL.3 TAP
1.25 DEEP
Ø 9.45
SLINGER
RODENT SCREENS
EA. END
(WHEN REQ'D)
6 HOLES
Ø.53
8.25
.63
10.00
4.76
11.25
Ø 11.51
9.64
5.75
1 LIFTING LUG
(EA. END)
DIAGONALLY SPACED
45°
45°
12.00
6.27
6.21
LEAD
HOLE
Ø1.75
.25
4 HOLES
.50-13 TAP
ON Ø7.25 B.C.
5.00
5.00
7.69
5.58
11.15
INT SH GND
BP5303
PU BRG RET DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHGD RODENT SCREENS LEAD TO ADD (WHEN REQ'D)
REV: C
VERSION: 03
REVISED: 03:24:15 03/21/2023
TDR: 000001206208
MODEL NO. 39LYE447
REF: -
BY: ENSHAB0
B
BALDOR - RELIANCE®
HORZ OPSB 254-6JM W/AEGIS INTERNAL SH GND
39LYE447

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1