ABB BALDOR RELIANCE

Customer information packet

EHM3311T-8

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3734M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/9/2026 1:39:14 PM

Specifications

Enclosure	OPSB
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	23.300 A @ 200.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	23.3 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	L
Type	AC
Mech. spec.	37J637
Base	
Status	PRD/A
Elec. spec.	37WGZ613
Layout	37LYJ637
Eff. date	07-10-2025
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	03-14-2016

KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3734M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	16.32 IN
Power Factor	77
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2094E06B03									
CAT.NO.	EHM3311T-8								
SPEC.	37J637Z613G1								
HP	7.5								
VOLTS	200								
AMPS	23.3								
RPM	1770								
FRAME	213T	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	J	**DES**	A	**CL**	F		
NEMA-NOM-EFF	91	**PF**	77						
RATING	40C AMB-CONT								
CC	010A			**USABLE AT 208V**		N/A			
DE	6307	**ODE**	6206						
AUTO	N	**MANUAL**	N	**NONE**	Y				
ENCL	OPSB	**SN**							
BLANK	SFA 26								

AC Induction Motor Performance Data
Record # 57432
Typical performance - not guaranteed values

Winding: 37WGZ613-R001	**Type:** 3734M	**Enclosure:** OPSB

Nameplate Data				**200 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	22.2 LB-FT
Volts			200	**Start Configuration**	direct on line
Full Load Amps			23.3	**Breakdown Torque**	72 LB-FT
R.P.M.			1770	**Pull-up Torque**	34 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	42.9 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	168 A
Service Factor (S.F.)			1.15	**No-load Current**	11.8 A
NEMA Nom. Eff.	91	**Power Factor**	77	**Line-line Res. @ 25ºC**	0.29 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	35°C
S.F. Amps				**Temp. Rise @ S.F. Load**	43°C
				Locked-rotor Power Factor	39.9
				Rotor inertia	0.836 LB-FT2

Load Characteristics 200 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	38	59	71	77	81	82	79
Efficiency	84.6	90.2	91.1	91.1	90.5	89	90.7
Speed	1794	1788	1780	1774	1765	1755	1769
Line amperes	12.8	15.2	18.8	22.9	27.6	32.9	25.7

ABB Motors and Mechanical Inc.

WINDING # 37WGZ613

7.5 HP 3 PH 60 HZ 1770 RPM 200 V 3734M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=72 PU=34 LR=42.9 LRA=168




37LYJ637
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
GREASE PLUG
(EA. END)
3.88
3.38
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.57
8.00
GREASE PLUG
(EA. END)
Ø9.57
7.90
LIFTING LUG
(1 EA. END)
4 HOLES
#5-40 TAP
.25 DEEP
Ø3.50 B.C.
W/SCREWS
10.04
35°
5.25
5.19
LEAD
HOLE
Ø1.38
2 HOLES
#6-32 TAP
.31 DEEP
Ø 1.783 B.C.
W/SCREWS
35°
4.25
4.25
6.72
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD 6-32 TAP HOLE CALLOUT
REV: E
VERSION: 05
REVISED: 12:23:27 03/21/2024
TDR: 000001227383
MODEL NO. 37LYJ637
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
HORZ 213-5T OPSB M W/PLUGGED GRSR & REL(HVAC), AEGIS MNT
37LYJ637

CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1