ABB BALDOR RELIANCE

Customer information packet

EHM3311T

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3734M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 8:29:08 AM

Specifications

Enclosure	OPSB
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	19.600 A @ 230.0 V
	20.600 A @ 208.0 V
	9.800 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	9.8 a

Part Detail

Revision	E
Type	AC
Mech. spec.	37J637
Base	
Status	PRD/A
Elec. spec.	37WGL863
Layout	37LYJ637
Eff. date	07-10-2025
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-10-2020

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3734M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	16.32 IN
Power Factor	79
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2094E06B03											
CAT.NO.	EHM3311T										
SPEC.	37J637L863G1										
HP	7.5										
VOLTS	230/460										
AMPS	19.6/9.8										
RPM	1770										
FRAME	213T	**HZ**	60		**PH**	3					
SER.F.	1.15	**CODE**	J	**DES**	A	**CL**	F				
NEMA-NOM-EFF	91	**PF**	79								
RATING	40C AMB-CONT										
CC	010A	**USABLE AT 208V**			N/A						
DE	6307	**ODE**	6206								
AUTO	N	**MANUAL**	N	**NONE**	Y						
ENCL	OPSB	**SN**									
BLANK	SFA 22.18/11.09										

AC Induction Motor Performance Data
Record # 85452
Preliminary Data Sheet

Winding: 37WGL863-R001 **Type:** 3734M **Enclosure:** OPSB

Nameplate Data			
Rated Output (HP)			7.5
Volts			230/460
Full Load Amps			19.6/9.8
R.P.M.			1770
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	J
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	91	**Power Factor**	79
Rating - Duty			40C AMB-CONT
S.F. Amps			22.0/11.0

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	22.2 LB-FT
Start Configuration	direct on line
Breakdown Torque	74.8 LB-FT
Pull-up Torque	37.1 LB-FT
Locked-rotor Torque	45.4 LB-FT
Starting Current	72 A
No-load Current	4.87 A
Line-line Res. @ 25ºC	1.67 Ω
Temp. Rise @ Rated Load	35°C
Temp. Rise @ S.F. Load	47°C
Locked-rotor Power Factor	45.8
Rotor inertia	0.836 lb-ft²

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	60	73	79	82	83	81
Efficiency	85	90.1	91.1	90.9	90.1	89	90.3
Speed	1793	1786	1779	1772	1764	1755	1766
Line amperes	5.34	6.47	7.99	9.87	11.9	14.2	11.1


ABB Motors and Mechanical Inc.


WINDING # 37WGL863

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 3734M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=74.8 PU=37.1 LR=45.4 LRA=72




37LYJ637
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
GREASE PLUG
(EA. END)
3.88
3.38
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.57
8.00
GREASE PLUG
(EA. END)
Ø9.57
7.90
LIFTING LUG
(1 EA. END)
4 HOLES
#5-40 TAP
.25 DEEP
Ø3.50 B.C.
W/SCREWS
10.04
35°
5.25
5.19
LEAD
HOLE
Ø1.38
2 HOLES
#6-32 TAP
.31 DEEP
Ø 1.783 B.C.
W/SCREWS
35°
4.25
4.25
6.72
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD 6-32 TAP HOLE CALLOUT
REV: E
VERSION: 05
REVISED: 12:23:27 03/21/2024
TDR: 000001227383
MODEL NO. 37LYJ637
REF: -
BY: ENSTEK0
B
BALDOR - RELIANCE®
HORZ 213-5T OPSB M W/PLUGGED GRSR & REL(HVAC), AEGIS MNT
37LYJ637

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS