

ABB BALDOR RELIANCE III



Customer information packet EJMM2542T-G

58M 2P OPSB HOR 324JM SE

Specifications

Enclosure	OPSB
Frame	324JM
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR NEMA PREMIUM CSA EEV CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	112.000 A @ 230.0 V 124.000 A @ 208.0 V 56.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	56.0 a

Part Detail

Revision	K
Type	AC
Mech. spec.	40E285
Base	
Status	PRD/A
Elec. spec.	40WGW803
Layout	40LYE285
Eff. date	12-11-2025
CD Diagram	CD0180
Poles	02
Leads	9#8
Proprietary	False
Created date	04-03-2019

Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP23
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4058M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	27.44 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3554LUA									
CAT.NO.	EJMM2542T-G			P/N				ENCL	OPSB
SPEC.	40E285W803G1	CC	010A	FRAME	324JM		SER.NO.		
HP	50		CLASS	H	HZ	60			
RPM	3525		PH	3	DES	A			
VOLTS	230/460		CODE	G	ODE BRG	6309	DE BRG	6312	
AMPS	112/56								
RATING	40C AMB-CONT		NEMA-NOM-EFF	93	GREASE	POLYREX EM			
PF	90	SER.F.	1.15		CT30-60(2:1) VT3-60(20:1)				
USABLE AT	50HZ 50HP 190/380V 138/69A			SF1.0					
HTR-VOLTS	HTR-AMPS		MAX. SPACE HEATER TEMP.						


ABB Motors and Mechanical Inc.

WINDING # 40WGW803


50 HP 3 PH 60 HZ 3525 RPM 460 V 4058M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=168 PU=115 LR=135 LRA=376




7/8/2026 ACPERF, record # 36101




CD0180



LOW VOLTAGE
(2D)



HIGH VOLTAGE
(1D)



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10: 25: 29 02/19/2019	BY: ENBRIRO
MTL: -	© □	

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1