

ABB BALDOR RELIANCE III

Customer information packet

EJMM3219T-G

7.5HP, 3450RPM, 3PH, 60HZ, 184JM, 3632M, OPSB

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	184JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.000 A @ 208.0 V 8.600 A @ 460.0 V 17.200 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	W
Type	AC
Mech. spec.	36T140
Base	
Status	PRD/A
Elec. spec.	36WGS516
Layout	36LYT140
Eff. date	06-01-2026
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	11-21-2011

Heater Indicator	No Heater
High Voltage Full Load Amps	8.6 a
Insulation Class	H
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3632M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.50 IN
Power Factor	89
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP3553L									
CAT.NO.	EJMM3219T-G								
SPEC	36T140S516G1								
HP	7.5								
VOLTS	230/460								
AMPS	17.2/8.6								
RPM	3450								
FRAME	184JM		HZ	60			PH	3	
SF	1.15	CODE	L	DES	A	CLASS	H		
NEMA NOM. EFF	88.5	PF	89						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	SER							
DE	6207		ODE	6205					
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									

AC Induction Motor Performance Data

Record # 36910

Typical performance - not guaranteed values

Winding: 36WGS516-R004			Type: 3632M		Enclosure: OPSB	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		7.5	Full Load Torque		11.3 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		18-17.2/8.6	Breakdown Torque		55.2 LB-FT	
R.P.M.		3450	Pull-up Torque		37 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		42.6 LB-FT	
NEMA Design Code		A KVA Code	Starting Current		86.3 A	
Service Factor (S.F.)		1.15	No-load Current		3.02 A	
NEMA Nom. Eff.		88.5 Power Factor	Line-line Res. @ 25°C		1.59 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		43°C	
S.F. Amps			Temp. Rise @ S.F. Load		53°C	
			Locked-rotor Power Factor		47	
			Rotor inertia		0.143 LB-FT2	

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	57	80	87	91	93	93	92
Efficiency	82.2	88.2	89.5	89.4	88.4	86.4	88.8
Speed	3572	3543	3513	3479	3443	3404	3457
Line amperes	3.68	4.98	6.72	8.63	10.7	13.1	9.87

ABB Motors and Mechanical Inc.

WINDING # 36WGS516

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 3450 RPM 460 V 3632M

TORQUES (LB-FT): PO=55.2 PU=37 LR=42.6 LRA=86.3





