ABB BALDOR RELIANCE

Customer information packet

EJMM3312T-G

10HP, 3500RPM, 3PH, 60HZ, 213JM, 3728M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 11:39:21 PM

Specifications

Enclosure	OPSB
Frame	213JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	26.000 A @ 208.0 V
	24.000 A @ 230.0 V
	12.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	E
Type	AC
Mech. spec.	37M556
Base	
Status	PRD/A
Elec. spec.	37WGL866
Layout	37LYM556
Eff. date	07-27-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	02-02-2021

Heater Indicator	No Heater
High Voltage Full Load Amps	12.0 a
Insulation Class	H
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.19 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	EJMM3312T-G								
SPEC.	37M556L866G1								
HP	10								
VOLTS	230/460								
AMPS	24/12								
RPM	3500								
FRAME	213JM	**HZ**	60			**PH**	3		
SF	1.15	**CODE**	H	**DES**	B	**CLASS**	H		
NEMA NOM. EFF	90.2	**PF**	85						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	**SN**							
DE	6309	**ODE**	6206						
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 10HP 190/380V 28.4/14.2A								SF1.0

AC Induction Motor Performance Data
Record # 86648
Preliminary Data Sheet

Winding: 37WGL866-R003	**Type:** 3728M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	15 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			24/12	**Breakdown Torque**	50.8 LB-FT
R.P.M.			3475	**Pull-up Torque**	23.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	29 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	81.5 A
Service Factor (S.F.)			1.15	**No-load Current**	4.72 A
NEMA Nom. Eff.	89.5	**Power Factor**	86	**Line-line Res. @ 25ºC**	0.991 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	33°C
S.F. Amps			27.6/13.8	**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	39.9
				Rotor inertia	0.255 lb-ft²

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	49	71	81	85	87	88	87
Efficiency	85	90	90.8	90.3	89.2	87.8	89.6
Speed	3576	3552	3527	3499	3469	3436	3479
Line amperes	5.5	7.27	9.53	12.1	15	18.2	13.8


ABB Motors and Mechanical Inc.


WINDING # 37WGL866

10 HP 3 PH 60 HZ 3475 RPM 460 V 3728M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=50.8 PU=23.7 LR=29 LRA=81.5




37LYM556
717-735 = 18.19
736-744 = 19.31
745-750 = 20.06
751-756 = 20.81
4.25
CHEK W/GAGE
T-9038
2.890
2.860
.640
.610
3.44
GREASE
FITTING
(EACH END)
.26
.19 KEY
1.38 LONG
NAMEPLATE
1.0000
.9995
8.500
8.497
9.09
.8745
.8740
Ø 1.250
1.248
.38-16 R.H. TAP
.88 DEEP
METAL
SLINGER
GREASE RELIEF
(EACH END)
6 HOLES
Ø .43
5.50
4.50
7.00
.50
8.00
INTERNAL
SHAFT GROUND
9.57
7.90
LIFTING LUG
(ONE EACH END)
45°
45°
10.03
5.25 +.00 -.06
LEAD HOLE
1.38 DIA.
4 HOLES
.50-13 TAP ON
Ø 7.25 B.C.
4.25
4.25
6.73
4.75
9.50
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: B
VERSION: 02
REVISED: 03:55:54 08/25/2022
TDR: 000001195814
MODEL NO. 37LYM556
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
HORZ 213-5JM OPSB M W/AEGIS INT SHAFT GRD
37LYM556

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS