ABB BALDOR RELIANCE

Customer information packet

EJMM3312T

10HP, 3500RPM, 3PH, 60HZ, 213JM, 3728M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/11/2026 5:33:25 AM

Specifications

Enclosure	OPSB
Frame	213JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.000 A @ 230.0 V
	26.000 A @ 208.0 V
	12.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	E
Type	AC
Mech. spec.	37F784
Base	
Status	PRD/A
Elec. spec.	37WGL866
Layout	37LYF784
Eff. date	06-11-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	11-11-2020

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	18.19 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3553LUA										
CAT.NO.	EJMM3312T									
SPEC.	37F784L866G1									
HP	10									
VOLTS	208-230/460									
AMPS	26-24/12									
RPM	3500									
FRAME	213JM	**HZ**	60			**PH**	3			
SF	1.15	**CODE**	H	**DES**	B	**CLASS**	F			
NEMA NOM. EFF	90.2	**PF**	85							
RATING	40C AMB-CONT									
CC	010A									
ENCL	OPSB	**SN**								
DE	6309	**ODE**	6206							
VPWM INVERTER READY										
CT30-60(2:1) VT3-60(20:1)										
USABLE AT	50HZ 10HP 190/380V 28.4/14.2A									SF1.0

AC Induction Motor Performance Data
Record # 85554
Preliminary Data Sheet

Winding: 37WGL866-R001	**Type:** 3728M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	15 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			25.6-24/12	**Breakdown Torque**	50.8 LB-FT
R.P.M.			3475	**Pull-up Torque**	23.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	29 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	81.5 A
Service Factor (S.F.)			1.15	**No-load Current**	4.72 A
NEMA Nom. Eff.	89.5	**Power Factor**	86	**Line-line Res. @ 25ºC**	0.991 Ω
Rating - Duty			50C AMB-CONT	**Temp. Rise @ Rated Load**	33°C
S.F. Amps			30.0-27.6/13.8	**Temp. Rise @ S.F. Load**	41°C
				Locked-rotor Power Factor	39.9
				Rotor inertia	0.255 lb-ft²

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	49	71	81	85	87	88	87
Efficiency	85	90	90.8	90.3	89.2	87.8	89.6
Speed	3576	3552	3527	3499	3469	3436	3479
Line amperes	5.5	7.27	9.53	12.1	15	18.2	13.8


ABB Motors and Mechanical Inc.


WINDING # 37WGL866

10 HP 3 PH 60 HZ 3475 RPM 460 V 3728M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=50.8 PU=23.7 LR=29 LRA=81.5




37LYF784
717-735 = 18.19
736-744 = 19.32
745-750 = 20.07
751-756 = 20.82
4.25
CHECK
W/GAUGE T-9038
2.890
2.860
.26
.640
.610
.188 KEYWAY
1.69 LONG
ENDMILLED
(KEY
1.38 LONG)
3.44
GREASE FITTING
(EA. END)
NAMEPLATE
Ø9.09
Ø 1.0000
.9995
Ø 1.250
1.248
Ø .8745
.8740
Ø8.500
8.497
.38-16 R.H.TAP
.88 DEEP
6 HOLES
Ø.43
5.50
.50
7.00
4.25
8.00
GREASE RELIEF
(EA. END)
Ø9.57
7.90
45°
45°
4 HOLES
.50-13 TAP ON
Ø7.25 B.C.
LIFTING LUG
(1 EA. END)
10.03
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.72
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: J
VERSION: 03
REVISED: 10:13:02 10/11/2022
TDR: 000001197758
MODEL NO. 37LYF784
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5JM OPSB 37M SUPER-E
37LYF784

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS