ABB BALDOR RELIANCE

Customer information packet

EJMM3546T-G

1HP, 1770RPM, 3PH, 60HZ, 143JM, 3520M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 5:48:48 AM

Specifications

Enclosure	TEFC
Frame	143JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.200 A @ 230.0 V
	3.200 A @ 208.0 V
	1.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	L
Type	AC
Mech. spec.	35E1603
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYE1603
Eff. date	04-15-2026
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	01-10-2022

Heater Indicator	No Heater
High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.43 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EJMM3546T-G								
SPEC	35E1603G004G1								
HP	1								
VOLTS	230/460								
AMPS	3.26/1.63								
RPM	1760								
FRAME	143JM	**HZ**	60			**PH**	3		
SF	1.15	**CODE**	N	**DES**	B	**CLASS**	H		
NEMA NOM. EFF	85.5	**PF**	67						
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	**SER**							
DE	6206	**ODE**	6203						
VPWM INVERTER READY	SFA 3.52/1.76								
CT6-60H(10:1)VT3-60H(20:1									
	50HZ 1HP 190/380V 3.6/1.8A								SF1.0


AC Induction Motor Performance Data
Record # 86922
Typical performance - not guaranteed values


Winding: 35WGG004-R004	**Type:** 3520M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	2.97 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			3.26/1.63	**Breakdown Torque**	13.68 LB-FT
R.P.M.			1760	**Pull-up Torque**	7.85 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	9.01 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	14.13 A
Service Factor (S.F.)			1.15	**No-load Current**	1.08 A
NEMA Nom. Eff.	85.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	16.9 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	24°C
S.F. Amps			3.52/1.76	**Temp. Rise @ S.F. Load**	27°C
				Locked-rotor Power Factor	61.5
				Rotor inertia	0.144 lb-ft²


Load Characteristics 460 V, 60 Hz, 1 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	30	47	60	69	76	79	73
Efficiency	72.1	81.7	84.7	85.7	85.5	84.7	85.6
Speed	1791	1784	1776	1768	1759	1750	1763
Line amperes	1.11	1.22	1.38	1.59	1.82	2.09	1.73


ABB Motors and Mechanical Inc.
WINDING # 35WGG004
Typical performance - not guaranteed values.
1 HP 3 PH 60 HZ 1760 RPM 460 V 3520M
TORQUES(LB-FT): PO=13.68 PU=7.85 LR=9.01 LRA=14.13
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1 HP)
11/15/2026 ACPERF, record # 86922


35LYE1603
510-528 = 15.41
529-535 = 16.29
536-546 = 17.66
4.281
4.219
CHECK WITH GAUGE T-9038
2.890
2.860
.640
.610
.13
3.75
.19 KEY
1.38 LONG
Ø7.19
NAMEPLATE
6.54
Ø4.500
4.497
Ø1.0000
.9995
Ø.8745
.8740
Ø1.156
1.154
SLINGER
6 HOLES
Ø.34
4.00
2.88
5.00
.50
5.94
.38-16 UNC
CL 3 R.H. TAP
.88 DEEP
6.61
5.68
45°
45°
6.81
3.50
3.44
4 HOLES
.38-16 TAP ON
Ø5.88 B.C.
LEAD HOLE
Ø.88
2.75
2.75
4.56
3.25
6.50
AEGIS SHAFT GROUND
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: OMIT GREASE FITTING AND RELIEF CALLOUT
REV: D
VERSION: 04
REVISED: 01:08:49 04/20/2022
TDR: 000001189638
MODEL NO. 35LYE1603
REF: -
BY: ENCHAL0
B
BALDOR - RELIANCE®
HORZ 143-5JM TEFC 35M W/AEGIS INTERNAL SHAFT GROUND
SH 1 of 1
35LYE1603

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS