

ABB BALDOR RELIANCE III

Customer information packet

EJMM3550T-5

1.5HP, 3500RPM, 3PH, 60HZ, 143JM, 3520M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	143JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.500 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	B

Part Detail

Revision	J
Type	AC
Mech. spec.	35T921
Base	
Status	PRD/A
Elec. spec.	35WGM784
Layout	35LYT921
Eff. date	02-07-2025
CD Diagram	CD0006
Poles	02
Leads	3#18
Proprietary	False
Created date	08-13-2015

Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	15.41 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L											
CAT.NO.	EJMM3550T-5										
SPEC.	35T921M784G1										
HP	1.5										
VOLTS	575										
AMP	1.5										
RPM	3500										
FRAME	143JM		HZ	60				PH	3		
SER.F.	1.15	CODE	L	DES	B	CL	B				
NEMA-NOM-EFF	84	PF	85								
RATING	40C AMB-CONT										
CC	010A										
DE	6206		ODE	6203							
ENCL	TEFC	SN									
VPWM INVERTER READY											
CT6-60H(10:1)VT3-60H(20:1											

AC Induction Motor Performance Data

Record # 52207

Typical performance - not guaranteed values

Winding: 35WGM784-R009			Type: 3520M		Enclosure: TEFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		1.5	Full Load Torque		2.22 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		1.5	Breakdown Torque		9.53 LB-FT		
R.P.M.		3500	Pull-up Torque		3.63 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		7.39 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		14.4 A
Service Factor (S.F.)		1.15	No-load Current		0.763 A		
NEMA Nom. Eff.		84	Power Factor	85	Line-line Res. @ 25°C		19.2 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		44°C	
S.F. Amps				Temp. Rise @ S.F. Load		51°C	
				Locked-rotor Power Factor		60.7	
				Rotor inertia		0.0553 LB-FT2	

Load Characteristics 575 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	44	66	78	85	89	90	87
Efficiency	72.1	82.1	84.3	84.6	84.2	82.7	84.4
Speed	3575	3552	3527	3499	3467	3434	3480
Line amperes	0.839	1.01	1.25	1.54	1.86	2.24	1.73


ABB Motors and Mechanical Inc.


WINDING # 35WGM784

Typical performance - not guaranteed values.


1.5 HP 3 PH 60 HZ 3500 RPM 575 V 3520M

TORQUES (LB-FT): PO=9.53 PU=3.63 LR=7.39 LRA=14.4





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1