

ABB BALDOR RELIANCE III

Customer information packet

EL11308

.75HP, 1160RPM, 1PH, 60HZ, 56H, 3530LC, OPEN, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56H
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 208.0 V @ 60 HZ 115.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.300 A @ 115.0 V 3.500 A @ 208.0 V 3.200 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.2 a

Part Detail

Revision	E
Type	AC
Mech. spec.	35E007
Base	
Status	PRD/A
Elec. spec.	35WGG064
Layout	35LYE007
Eff. date	01-09-2026
CD Diagram	CD0055
Poles	06
Leads	6#18
Proprietary	False
Created date	08-01-2022

Insulation Class	F
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	H
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3530LC
Mounting Arrangement	F1
Number of Poles	6
Overall Length	12.62 IN
Power Factor	95
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1160 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3155L											
CAT.NO.	EL11308										
SPEC.	35E007G064										
HP	.75										
VOLTS	115/208-230										
AMP	6.3/3.5-3.2										
RPM	1160										
FRAME	56H		HZ	60				PH	1		
SER.F.	1.00	CODE	H	DES	L	CL	F				
F.L. AVG. EFF.	81.5	PF	95								
RATING	40C AMB-CONT										
CC											
DE	6205		ODE	6203							
ENCL	OPEN	SN									

AC Induction Motor Performance Data

Record # 88896

Typical performance - not guaranteed values

Winding: 35WGG064-R003			Type: 3530LC		Enclosure: OPEN	
Nameplate Data			115 V, 60 Hz: Low Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		3.4 LB-FT	
Volts		115/208-230	Start Configuration		direct on line	
Full Load Amps		6.3/3.5-3.2	Breakdown Torque		8.03 LB-FT	
R.P.M.		1160	Pull-up Torque		5.18 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque		11.2 LB-FT
NEMA Design Code		L	KVA Code		H	
Service Factor (S.F.)		1	No-load Current		1.97 A	
NEMA Nom. Eff.		81.5	Power Factor		95	
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load 39°C	
					Locked-rotor Power Factor 98.1	
					Rotor inertia 0.217 lb-ft ²	

Load Characteristics 115 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	84	91	94	95	95	93
Efficiency	54.8	72.8	79.9	81.6	79.7	73.7
Speed	1190	1182	1172	1160	1143	1115
Line amperes	2.66	3.66	4.84	6.28	8.03	10.6


ABB Motors and Mechanical Inc.

WINDING # 35WGG064


Typical performance - not guaranteed values.

0.75 HP 1 PH 60 HZ 1160 RPM 115 V 3530LC

TORQUES (LB-FT): PO=8.03 PU=5.18 LR=11.2 LRA=44.2



8/23/2026 ACPERF, record # 88896



CD0055

