

ABB BALDOR RELIANCE III

Customer information packet

EJMM4103T-G

54M 4P TEFC HOR 284JM SE

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	284JM
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	64.000 A @ 208.0 V 62.000 A @ 230.0 V 31.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	K
Type	AC
Mech. spec.	10H520
Base	
Status	PRD/A
Elec. spec.	10WGZ651
Layout	10LYH520
Eff. date	12-11-2025
CD Diagram	CD0180
Poles	04
Leads	9#10
Proprietary	False
Created date	04-02-2019

Heater Indicator	No Heater
High Voltage Full Load Amps	31.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1054M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	28.64 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3443LUA													
CAT.NO.	EJMM4103T-G				CUST. P/N				ENCL				TEFC
SPEC.	10H520Z651G2	CC	010A	FRAME	284JM	SER.NO.							
HP	25		CLASS	H	HZ	60							
R.P.M.	1775		PH.	3	DES.	A							
VOLTS	230/460			CODE	J	ODE BRG	6309	DE BRG	6312				
AMPS	62/31												
RATING	40C AMB-CONT		NEMA NOM. EFF.			93.6	GREASE		POLYREX EM				
P.F.	81	SER.F.	1.15	CT6-60H(10:1)VT3-60H(20:1									
USABLE AT	50HZ 25HP 190/380V 72/36A			SF1.0									
VOLTS	AMPS	MAX. SPACE HEATER TEMP.											

AC Induction Motor Performance Data

Record # 67463

Typical performance - not guaranteed values

Winding: 10WGZ651-R005			Type: 1054M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		25		Full Load Torque		74.02 LB-FT
Volts		230/460		Start Configuration		direct on line
Full Load Amps		62/31		Breakdown Torque		262 LB-FT
R.P.M.		1775		Pull-up Torque		118 LB-FT
Hz	60	Phase	3	Locked-rotor Torque		142 LB-FT
NEMA Design Code		A	KVA Code	Starting Current		223 A
Service Factor (S.F.)		1.15		No-load Current		13.6 A
NEMA Nom. Eff.		93.6	Power Factor	Line-line Res. @ 25°C		0.2345 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		51°C
S.F. Amps				Temp. Rise @ S.F. Load		61°C
				Locked-rotor Power Factor		30.6

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	43	65	76	81	84	85	83
Efficiency	88.3	92.8	93.9	94	93.7	93.1	93.8
Speed	1794.1	1789.3	1783.5	1777.8	1770.8	1763.8	1774
Line amperes	15.3	19.3	24.6	30.6	37.2	44.5	34.6


ABB Motors and Mechanical Inc.


WINDING # 10WGZ651

Typical performance - not guaranteed values.


25 HP 3 PH 60 HZ 1775 RPM 460 V 1054M

TORQUES (LB-FT): PO=262 PU=118 LR=142 LRA=223







CD0180



LOW VOLTAGE
(2D)



HIGH VOLTAGE
(1D)



NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: -



BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1