

ABB BALDOR RELIANCE III

Customer information packet

EJPM2534T

30HP, 3510RPM, 3PH, 60HZ, 284JP, 3948M, OPSB, F

Class -

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	284JP
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA EEV UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	33.000 A @ 460.0 V 66.000 A @ 230.0 V 74.000 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	U
Type	AC
Mech. spec.	39E303
Base	
Status	PRD/A
Elec. spec.	39WGX286
Layout	39LYE303
Eff. date	06-26-2024
CD Diagram	CD0005
Poles	02
Leads	9#8
Proprietary	False
Created date	05-05-2009

High Voltage Full Load Amps	33.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3948M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	29.44 IN
Power Factor	92
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
Service Factor	1.15
Shaft Diameter	1.750 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3510 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA												
CAT.NO.	EJPM2534T				P/N					ENCLOSURE		OPSB
SPEC.	39E303X286			CC	010A	FRAME		284JP	S/N			
HP	30				CLASS		F	HZ	60			
RPM	3510				PH	3	DES		B			
VOLT	230/460				KVA-CODE			F	ODE BRG	6208	DE BRG	6312
AMP	66/33											
RATING	40C AMB-CONT				GREASE		POLYREX EM					
NEMA-NOM-EFF	91.7	PF	92	SER.F.	1.15							
	50HZ 30HP 190/380V 82/41A						SF1.0					
HTR-VOLTS	HTR-AMPS											

AC Induction Motor Performance Data

Record # 13125

Typical performance - not guaranteed values

Winding: 39WGX286-R001			Type: 3948M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		30	Full Load Torque		45 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		66/33	Breakdown Torque		148 LB-FT		
R.P.M.		3510	Pull-up Torque		53 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		67.5 LB-FT	
NEMA Design Code		B	KVA Code	F	Starting Current		207 A
Service Factor (S.F.)		1.15	No-load Current		7.51 A		
NEMA Nom. Eff.		91.7	Power Factor	92	Line-line Res. @ 25°C		0.342 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		38°C
S.F. Amps					Temp. Rise @ S.F. Load		48°C
					Locked-rotor Power Factor		28
					Rotor inertia		1.23 LB-FT2

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	70	87	91	92	92	92	92
Efficiency	89.4	92.5	92.6	91.8	90.7	89	91.1
Speed	3577	3555	3531	3505	3478	3443	3489
Line amperes	10.9	17.2	24.9	33.1	41.7	51.8	38.26

ABB Motors and Mechanical Inc.

WINDING # 39WGX286

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 3510 RPM 460 V 3948M

TORQUES (LB-FT): PO=148 PU=53 LR=67.5 LRA=207





