

ABB BALDOR RELIANCE III

Customer information packet EM2276T

7.5HP, 1180RPM, 3PH, 60HZ, 254T, 0954M, TEFC, F

Part Detail


Revision	AN
Type	AC
Mech. spec.	09P11
Base	
Status	PRD/A
Elec. spec.	09WGT118
Layout	09LYP011
Eff. date	03-19-2024
CD Diagram	CD0005
Poles	06
Leads	9#12
Proprietary	False
Created date	08-21-2014

Nameplate




NP3441LUA									
CAT.NO.	EM2276T								
SPEC	09P011T118								
HP	7.5								
VOLTS	230/460								
AMPS	22/11								
RPM	1180								
FRAME	254T		HZ	60		PH	3		
SF	1.15	CODE	J	DES	A	CLASS	F		
NEMA NOM. EFF	91		PF	70					
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6309		ODE	6208					
VPWM INVERTER READY	SFA 24.5/12.3								
CT6-60H(10:1)VT3-60H(20:1									
	50Hz 7.5HP 190/380V 25/12.5A								
	SF1.0								

Accessories

Part number	Description	Multiplier
09-1309	C FACE KIT	A8



CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005