

ABB BALDOR RELIANCE III

Customer information packet

EJPM3615T

5HP, 1750RPM, 3PH, 60HZ, 184JP, 3644M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184JP
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.200 A @ 208.0 V 6.900 A @ 460.0 V 13.800 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	G
Type	AC
Mech. spec.	36R059
Base	
Status	PRD/A
Elec. spec.	36WGR639
Layout	36LYR059
Eff. date	05-12-2026
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	05-19-2015

Heater Indicator	No Heater
High Voltage Full Load Amps	6.9 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3644M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	22.61 IN
Power Factor	76
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP3441LUA									
CAT.NO.	EJPM3615T								
SPEC	36R059R639G1								
HP	5								
VOLTS	230/460								
AMPS	13.8/6.9								
RPM	1750								
FRAME	184JP		HZ	60			PH	3	
SF	1.15		CODE	K	DES	A	CLASS	F	
NEMA NOM. EFF	89.5		PF	76					
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6207		ODE	6205					
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									
50Hz 5HP 190/380V 16/8A									SF1.0

AC Induction Motor Performance Data

Record # 53352

Typical performance - not guaranteed values

Winding: 36WGR639-R004			Type: 3644M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		5	Full Load Torque		14.9 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		13.8/6.9	Breakdown Torque		57 LB-FT			
R.P.M.		1750	Pull-up Torque		34.6 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		38.3 LB-FT		
NEMA Design Code		A	KVA Code	K	Starting Current		53.8 A	
Service Factor (S.F.)		1.15	No-load Current		3.62 A			
NEMA Nom. Eff.		89.5	Power Factor		76	Line-line Res. @ 25°C		2.12 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		71°C	
S.F. Amps			Temp. Rise @ S.F. Load		85°C			
			Rotor inertia		0.41 LB-FT2			

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	36	57	69	76	81	82	79
Efficiency	83.9	89.2	90.3	89.7	89	87.3	89.3
Speed	1790	1778	1765	1753	1737	1720	1743
Line amperes	3.91	4.62	5.69	6.86	8.09	9.73	7.6

ABB Motors and Mechanical Inc.

WINDING # 36WGR639

Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 1750 RPM 460 V 3644M

TORQUES (LB-FT): PO=57 PU=34.6 LR=38.3 LRA=53.8





