Customer information packet

EL11206

.33HP, 1740RPM, 1PH, 60HZ, 48, 3418LC, ODP, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 11:21:28 PM

Specifications

Enclosure	ODP
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.330 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 230.0 V
	2.500 A @ 208.0 V
	3.400 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a

Part Detail

Revision	M
Type	AC
Mech. spec.	34F351
Base	
Status	PRD/A
Elec. spec.	34WGW954
Layout	34LYF351
Eff. date	12-31-2024
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	03-11-2014

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3418LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	9.76 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3155L									
CAT.NO.	EL11206								
SPEC.	34F351W954G2								
HP	.33								
VOLTS	115/230								
AMP	3.4/1.7								
RPM	1740								
FRAME	48	**HZ**	60				**PH**	1	
SER.F.	1.35	**CODE**	K	**DES**	N	**CL**	F		
F.L. AVG. EFF.	72.4	**PF**	85						
RATING	40C AMB-CONT								
CC									
DE	6203	**ODE**	6203						
ENCL	ODP	**SN**							
	SFA 4.4/2.2								

AC Induction Motor Performance Data
Record # 44912
Typical performance - not guaranteed values

Winding: 34WGW954-R003	**Type:** 3418LC	**Enclosure:** OPEN

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.33	**Full Load Torque**	0.996 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			3.4/1.7	**Breakdown Torque**	3.18 LB-FT
R.P.M.			1740	**Pull-up Torque**	2.29 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	4.26 LB-FT
NEMA Design Code	-	**KVA Code**	K	**Starting Current**	24.1 A
Service Factor (S.F.)			1.35	**No-load Current**	1.69 A
NEMA Nom. Eff.	72.4	**Power Factor**	85	**Line-line Res. @ 25ºC**	1.7428 Ω A Ph 5.5858 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	35°C
S.F. Amps			4.4/2.2	**Temp. Rise @ S.F. Load**	42°C

Load Characteristics 115 V, 60 Hz, 0.33 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	62	72	81	85	87	89	88
Efficiency	32.1	64.5	69.3	73.5	76.7	73.7	75.5
Speed	1780.3	1770	1754.7	1739.9	1725.3	1703.3	1716
Line amperes	1.96	2.31	2.87	3.43	3.99	4.81	4.32


ABB Motors and Mechanical Inc.

WINDING # 34WGW954


0.33 HP 1 PH 60 HZ 1740 RPM 115 V 3418LC

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=3.18 PU=2.29 LR=4.26 LRA=24.1



11/14/2026 ACPERF, record # 44912


34LYF351
408-421 = 9.76
422-428 = 10.63
429-432 = 11.13
1.75
1.50
1.12
FLAT
NAMEPLATE
.453
.433
Ø .5000
.4995
1.82
.63
4 SLOTS
.34 WIDE
2.75
2.50
4.00
Ø5.68
5.07
4.03
2.28
5.80
3.00
2.94
THERMAL
(WHEN
REQ'D)
LEAD HOLE
Ø .88
2.13
2.13
3.54
2.88
5.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CLEAN UP DIMENSIONING
REV: E
VERSION: 04
REVISED: 10:32:08 10/02/2025
TDR: 000001264465
MODEL NO. 34LYF351
REF: -
BY: ENJEFD0
B
BALDOR - RELIANCE®
STD HOR 34LC NEMA 48 OPEN
34LYF351

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS