ABB BALDOR RELIANCE

Customer information packet

EM2333T-5G

15HP, 1765RPM, 3PH, 60HZ, 254T, 0944M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/9/2026 1:51:04 PM

Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR
	CSA
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.600 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.6 a
Insulation Class	H

Part Detail

Revision	AL
Type	AC
Mech. spec.	09J359
Base	
Status	PRD/A
Elec. spec.	09WGT124
Layout	09LYJ359
Eff. date	03-12-2026
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	10-23-2015

Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.30 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L									
CAT.NO.	EM2333T-5G								
SPEC.	09J359T124G1								
HP	15								
VOLTS	575								
AMP	14.6								
RPM	1765								
FRAME	254T	**HZ**	60				**PH**	3	
SER.F.	1.15	**CODE**	H	**DES**	A	**CL**	H		
NEMA-NOM-EFF	92.4	**PF**	83						
RATING	40C AMB-CONT								
CC	010A								
DE	6309	**ODE**	6208						
ENCL	TEFC	**SN**							
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									

AC Induction Motor Performance Data
Record # 47379
Typical performance - not guaranteed values

Winding: 09WGT124-R002	**Type:** 0944M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			15	**Full Load Torque**	44.5 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			14.6	**Breakdown Torque**	153 LB-FT
R.P.M.			1765	**Pull-up Torque**	69.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	86.5 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	102 A
Service Factor (S.F.)			1.15	**No-load Current**	6.05 A
NEMA Nom. Eff.	92.4	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.874 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	54°C
S.F. Amps				**Temp. Rise @ S.F. Load**	66°C
				Locked-rotor Power Factor	33.1
				Rotor inertia	1.92 LB-FT2

Load Characteristics 575 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	69	78	83	85	87	86
Efficiency	88.1	92.3	92.6	92.4	91.5	90.5	92.2
Speed	1791	1783	1774	1765	1755	1743	1769
Line amperes	6.9	8.8	11.6	14.6	18.1	21.5	16.3

ABB Motors and Mechanical Inc.

WINDING # 09WGT124

15 HP 3 PH 60 HZ 1765 RPM 575 V 0944M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=153 PU=69.5 LR=86.5 LRA=102



9/9/2026 ACPERF, record # 47379


09LYJ359
(920 - 960) = 23.36
10.11
4.32
4.00
.38 KEY
2.88 LONG
Ø 1.625
1.624
SLINGER
EA. END
(WHEN REQ'D)
8 HOLES
Ø.53
8.25
8.25
.75
10.00
4.25
11.50
DRAIN FITTING
(EA. END)
12.94
10.18
6.63
2.71
12.87
6.25
6.19
3.50
.79
LEAD HOLE
Ø1.75
5.00
5.00
8.18
5.75
11.50
INT SH GND
BP5303
PU BRG RETAINER DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: REVISED TO UPDATE SLINGER LEADER
REV: K
VERSION: 10
REVISED: 10:12:59 09/19/2022
TDR: 000001197243
MODEL NO. 09LYJ359
REF: -
BY: USSADEL11
B
BALDOR - RELIANCE®
HORZ TEFC 254-6T W/INT SH GND
09LYJ359

CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1