

**BALDOR • RELIANCE**

---

# Customer information packet

## EM2539T-5G

40HP, 1770RPM, 3PH, 60HZ, 324T, 4064M, OPSB, F1

## Specifications

Enclosure	OPSB
Frame	324T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	40.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	40.0 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	H

## Part detail

Revision	N
Type	AC
Mech. spec.	40E245
Base	
Status	PRD/A
Elec. spec.	40WGX786
Layout	40LYE245
Eff. date	08-01-2023
CD Diagram	CD0006
Poles	04
Leads	3#8
Proprietary	False
Created date	09-11-2013

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4064M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.19 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

**NP3554L**

<b>CAT.NO.</b>	EM2539T-5G	<b>P/N</b>		<b>ENCL</b>	OPSB
<b>SPEC.</b>	40E245X786G1	<b>CC</b>	010A	<b>FRAME</b>	324T
<b>HP</b>	40	<b>CLASS</b>	H	<b>HZ</b>	60
<b>RPM</b>	1770	<b>PH</b>	3	<b>DES</b>	A
<b>VOLTS</b>	575	<b>CODE</b>	H	<b>ODE BRG</b>	6309
<b>AMPS</b>	40	<b>USABLE AT 208V</b>	N/A	<b>DE BRG</b>	6312
<b>RATING</b>	40C AMB-CONT	<b>NEMA-NOM-EFF</b>	94.1	<b>GREASE</b>	POLYREX EM
<b>PF</b>	81	<b>SER.F.</b>	1.15	<b>VPWM INVERTER READY</b>	
<b>HTR-VOLTS</b>	<b>HTR-AMPS</b>	<b>MAX. SPACE HEATER TEMP.</b>			

**AC Induction Motor Performance Data**

Record # 50231

Typical performance - not guaranteed values

Winding: 40WGX786-R002		Type: 4064M		Enclosure: OPSB	
<b>Nameplate Data</b>			<b>575 V, 60 Hz: Single Voltage Motor</b>		
Rated Output (HP)	40	Full Load Torque	119 LB-FT		
Volts	575	Start Configuration	direct on line		
Full Load Amps	40	Breakdown Torque	438 LB-FT		
R.P.M.	1770	Pull-up Torque	192 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	253 LB-FT	
NEMA Design Code	A	KVA Code	H	Starting Current	272 A
Service Factor (S.F.)	1.15	No-load Current	17.9 A		
NEMA Nom. Eff.	94.1	Power Factor	81	Line-line Res. @ 25°C	0.224 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	41°C	
S.F. Amps			Temp. Rise @ S.F. Load	50°C	
			Locked-rotor Power Factor	32	
			Rotor inertia	5.09 LB-FT <sup>2</sup>	

**Load Characteristics 575 V, 60 Hz, 40 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	41	63	75	81	84	84	83
Efficiency	90.1	93.2	94	93.8	93.3	92.9	93.5
Speed	1793	1785	1778	1771	1763	1754	1766
Line amperes	20.3	25.5	32.1	39.6	48	57.4	44.6


ABB Motors and Mechanical Inc.

WINDING # 40WGX786


Typical performance - not guaranteed values.

40 HP 3 PH 60 HZ 1770 RPM 575 V 4064M


TORQUES (LB-FT): PO=438 PU=192 LR=253 LRA=272



5/29/2024 ACPERF, record # 50231



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

**BALDOR - RELIANCE®**

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1