

DUTY MASTER ALTERNATING CURRENT MOTORS
SQUIRREL-CAGE INDUCTION

ENCLOSURE: PROTECTED
MOUNTING: FOOT

FRAMES 364T-365T

COOLING: SELF-VENTILATED



617428-115

D

C

B

A



D

C

B

A

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END
OF SHAFT EXTENSION IS .003 T.I.R.

WEIGHT (LBS): 364T = 715
365T = 755

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE MODEL TO ADD EXTERNAL HARDWARE PER PROD MGM			
REV: A	VERSION: 01	REVISED: 10:14:50 10/04/2022	TDR: 000001196512
MODEL NO. 617428-115			REF: -
BY: ENFRAJ0			B

BALDOR

DIM SHT PROT SV FT 364-5T (611750-001)

617428-115