

BALDOR • RELIANCE

Customer information packet

EM2555T-5

100HP, 1780RPM, 3PH, 60HZ, 404T, 4484M, OPSB, F

Specifications

Enclosure	OPSB
Frame	404T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	100.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA PREMIUM (OLD LOGO) CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	93.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	93.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H

Part detail

Revision	S
Type	AC
Mech. spec.	44E012
Base	
Status	PRD/A
Elec. spec.	44WGW315
Layout	44LYE012
Eff. date	11-19-2024
CD Diagram	CD0006
Poles	04
Leads	3#4
Proprietary	False
Created date	08-06-2010

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4484M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	36.97 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138L

CAT.NO.	EM2555T-5	P/N		ENCLOSURE	OPSB		
SPEC.	44E012W315G1	CC	010A	FRAME	404T	S/N	
HP	100	CLASS	F	HZ	60		
RPM	1780	PH	3	DES	A		
VOLT	575	KVA-CODE	H	ODE BRG	6312	DE BRG	6316
AMP	93						
RATING	40C AMB-CONT	GREASE	POLYREX EM				
NEMA-NOM-EFF	95.4	PF	83	SER.F.	1.15		
HTR-VOLTS		HTR-AMPS					

AC Induction Motor Performance Data

Record # 32035

Typical performance - not guaranteed values

Winding: 44WGW315-R001		Type: 4484M		Enclosure: OPSB	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	100	Full Load Torque	295 LB-FT		
Volts	575	Start Configuration	direct on line		
Full Load Amps	93	Breakdown Torque	839 LB-FT		
R.P.M.	1780	Pull-up Torque	355 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque	471 LB-FT
NEMA Design Code	A	KVA Code	H	Starting Current	646 A
Service Factor (S.F.)	1.15	No-load Current	33.5 A		
NEMA Nom. Eff.	95.4	Power Factor	83	Line-line Res. @ 25°C	0.0697 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	47°C	
S.F. Amps			Temp. Rise @ S.F. Load	57°C	
			Locked-rotor Power Factor	25	
			Rotor inertia	15.9 LB-FT ²	

Load Characteristics 575 V, 60 Hz, 100 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	50	73	81	85	86	87	86
Efficiency	92.6	95.4	95.6	95.5	95.1	94.4	95.3
Speed	1794	1790	1785	1780	1775	1769	1777
Line amperes	40.1	53.9	72.1	92.7	115	137	106


ABB Motors and Mechanical Inc.

WINDING # 44WG315


Typical performance - not guaranteed values.

100 HP 3 PH 60 HZ 1780 RPM 575 V 4484M



TORQUES (LB-FT): PO=839 PU=355 LR=471 LRA=646



6/18/2026 ACPERF, record # 32035



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1