

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

FRAMES 404T-405T

COOLING: SELF-VENTILATED

ENCLOSURE: PROTECTED
MOUNTING: FOOT



617428-119

D

C

B

A



D

C

B

A

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END
OF SHAFT EXTENSION IS .003 T.I.R.

WEIGHT (LBS): 404T = 1045
405T = 1085

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: NEW TO REPLACE 404-5T ON 611750-501			
REV: -	VERSION: 00	REVISED: 08:12:43 06/09/2016	TDR: 000000983687
MODEL NO. 617428-119			REF: -
BY: ENWINB0			B

BALDOR

DIM SHT 404-5T (611750-501)

617428-119