

BALDOR • RELIANCE

Customer information packet

EM2534T-8

30HP, 3530RPM, 3PH, 60HZ, 284TS, 4040M, OPSB, F

Specifications

Enclosure	OPSB
Frame	284TS
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	78.000 A @ 208.0 V 80.000 A @ 200.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	80.0 a
Insulation Class	F

Part detail

Revision	K
Type	AC
Mech. spec.	40G49
Base	
Status	PRD/A
Elec. spec.	40WGX310
Layout	40LYG049
Eff. date	06-27-2024
CD Diagram	CD0695
Poles	02
Leads	6#6
Proprietary	False
Created date	08-12-2015

Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4040M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.44 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3530 rpm
Speed Code	Single Speed
Starting Method	Part Winding
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3554L

CAT.NO.	EM2534T-8	P/N		ENCL	OPSB
SPEC.	40G049X310G1	CC	010A	FRAME	284TS
HP	30	CLASS	F	HZ	60
RPM	3530	PH	3	DES	A
VOLTS	200	CODE	G	ODE BRG	6309
AMPS	80	DE BRG	6311		
RATING	40C AMB-CONT	NEMA-NOM-EFF	91.7	GREASE	POLYREX EM
PF	87	SER.F.	1.15	VPWM INVERTER READY	
HTR-VOLTS	HTR-AMPS	MAX. SPACE HEATER TEMP.			

Accessories

Part number	Description	Multiplier
40-1400	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 52218

Typical performance - not guaranteed values

Winding: 40WGX310-R001		Type: 4040M		Enclosure: OPSB	
Nameplate Data			200 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	30	Full Load Torque	44.7 LB-FT		
Volts	200	Start Configuration	direct on line		
Full Load Amps	80	Breakdown Torque	165 LB-FT		
R.P.M.	3530	Pull-up Torque	55.6 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	73.4 LB-FT	
NEMA Design Code	A KVA Code	G	Starting Current	518 A	
Service Factor (S.F.)	1.15	No-load Current	22.9 A		
NEMA Nom. Eff.	91.7 Power Factor	87	Line-line Res. @ 25°C	0.047 Ω	
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	23°C	
S.F. Amps			Temp. Rise @ S.F. Load	29°C	
			Locked-rotor Power Factor	24.2	
			Rotor inertia	1.72 LB-FT ²	

Load Characteristics 200 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	62	80	86	88	89	89	89
Efficiency	86.1	91.2	92.3	92.3	91.9	91	92.1
Speed	3582	3567	3552	3536	3518	3499	3525
Line amperes	30.7	44.8	61.1	79.6	99.1	120	91.3


ABB Motors and Mechanical Inc.

WINDING # 40WGx310


30 HP 3 PH 60 HZ 3530 RPM 200 V 4040M

Typical performance - not guaranteed values.



TORQUES (LB-FT): PO=165 PU=55.6 LR=73.4 LRA=518




3/26/2025 ACPERF, record # 52218




CD0695



START CONNECTION



RUN CONNECTION



NOTES:

1. MOTOR MAY BE WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0695

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 01/21/99 3:19	TDR: 0171435
S69000		FILE: AAA00005151	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, PART WINDING START