

ABB BALDOR RELIANCE III

Customer information packet

EM2535T-5BG

30HP, 1775RPM, 3PH, 60HZ, 286T, 4060M, OPSB, F1

Specifications

Enclosure	OPSB
Frame	286T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	29.0 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	H

Part Detail

Revision	N
Type	AC
Mech. spec.	40E332
Base	
Status	PRD/A
Elec. spec.	40WGX351
Layout	40LYE332
Eff. date	02-12-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	06-10-2016

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4060M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.81 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138L																	
CAT.NO.	EM2535T-5BG				P/N						ENCLOSURE		OPSB				
SPEC.	40E332X351G1			CC	010A		FRAME		286T		S/N						
HP	30				CLASS		H		HZ		60						
RPM	1775				PH		3		DES		A						
VOLT	575								KVA-CODE		H		ODE BRG		6309	DE BRG	6311
AMP	29																
RATING	40C AMB-CONT				GREASE		POLYREX EM										
NEMA-NOM-EFF	94.1	PF	82	SER.F.		1.15											
HTR-VOLTS			HTR-AMPS														

AC Induction Motor Performance Data

Record # 57367

Typical performance - not guaranteed values

Winding: 40WGX351-R002				Type: 4060M		Enclosure: OPSB	
Nameplate Data				575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		30		Full Load Torque		88.7 LB-FT	
Volts		575		Start Configuration		direct on line	
Full Load Amps		29		Breakdown Torque		278 LB-FT	
R.P.M.		1775		Pull-up Torque		129 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		160 LB-FT	
NEMA Design Code		A	KVA Code	H	Starting Current		200 A
Service Factor (S.F.)		1.15		No-load Current		12.2 A	
NEMA Nom. Eff.		94.1	Power Factor	82	Line-line Res. @ 25°C		0.328 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		29°C	
S.F. Amps				Temp. Rise @ S.F. Load		35°C	
				Locked-rotor Power Factor		31.5	
				Rotor inertia		4.77 LB-FT ²	

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	78	83	85	85	84
Efficiency	90.4	93.8	94.4	94.3	93.5	93	93.8
Speed	1794	1788	1782	1777	1770	1763	1773
Line amperes	14	17.9	23.1	28.9	35.4	42.4	32.8


ABB Motors and Mechanical Inc.


WINDING # 40WGX351

Typical performance - not guaranteed values.




30 HP 3 PH 60 HZ 1775 RPM 575 V 4060M

TORQUES (LB-FT): PO=278 PU=129 LR=160 LRA=200





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1