

ABB BALDOR RELIANCE III



Customer information packet EM2536T

30HP, 1180RPM, 3PH, 60HZ, 326T, 4084M, OPSB, F1

Specifications

Enclosure	OPSB
Frame	326T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	78.000 A @ 230.0 V 82.000 A @ 208.0 V 39.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	39.0 a

Part Detail

Revision	Z
Type	AC
Mech. spec.	40E212
Base	
Status	PRD/A
Elec. spec.	40WGX122
Layout	40LYE212
Eff. date	11-29-2023
CD Diagram	CD0005
Poles	06
Leads	9#8
Proprietary	False
Created date	06-03-2009

Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4084M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	28.69 IN
Power Factor	77
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA										
CAT.NO.	EM2536T		P/N				ENCLOSURE	OPSB		
SPEC.	40E212X122	CC	010A	FRAME	326T	S/N				
HP	30		CLASS	F	HZ	60				
RPM	1180		PH	3	DES	A				
VOLT	230/460		KVA-CODE	H		ODE BRG	6309	DE BRG	6312	
AMP	78/39									
RATING	40C AMB-CONT		GREASE	POLYREX EM						
NEMA-NOM-EFF	93.6	PF	77	SER.F.	1.15					
	50Hz 30Hp 190/380V 88/44A					SF 1.0				
HTR-VOLTS			HTR-AMPS							


ABB Motors and Mechanical Inc.


WINDING # 40WGx122

Typical performance - not guaranteed values.


30 HP 3 PH 60 HZ 1180 RPM 460 V 4084M

TORQUES (LB-FT): PO=417 PU=187 LR=233 LRA=267





CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005