

BALDOR • RELIANCE

Customer information packet

EM31111

.75HP, 3450RPM, 3PH, 60HZ, 56, 3416M, ODP, F1, N

Class - None

Division - Not Applicable

Specifications

Enclosure	ODP
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
XP Class and Group	None
XP Division	Not Applicable
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.200 A @ 460.0 V 2.400 A @ 230.0 V 2.700 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	76.8 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.2 a

Part detail

Revision	D
Type	AC
Mech. spec.	34B061
Base	
Status	PRD/A
Elec. spec.	34WGW719
Layout	34LYB061
Eff. date	04-22-2021
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	02-26-2014

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3416M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	10.25 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3155L									
CAT.NO.	EM31111								
SPEC.	34B061W719G1								
HP	.75								
VOLTS	230/460								
AMP	2.4/1.2								
RPM	3450								
FRAME	56		HZ	60		PH	3		
SER.F.	1.25	CODE	L	DES	B	CL	F		
F.L. AVG. EFF.	76.8	PF	80						
RATING	40C AMB-CONT								
CC			USABLE AT 208V				N/A		
DE	6203		ODE	6203					
ENCL	ODP	SN							
	SFA 2.8/1.4								

AC Induction Motor Performance Data

Record # 44882

Typical performance - not guaranteed values

Winding: 34WGW719-R009		Type: 3416M	Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)	.75	Full Load Torque	1.15 LB-FT		
Volts	230/460	Start Configuration	direct on line		
Full Load Amps	2.4/1.2	Breakdown Torque	5.62 LB-FT		
R.P.M.	3450	Pull-up Torque	3.98 LB-FT		
Hz	60 Phase	3	Locked-rotor Torque	5.14 LB-FT	
NEMA Design Code	B	KVA Code	L	Starting Current	9.2 A
Service Factor (S.F.)	1.25	No-load Current	0.611 A		
NEMA Nom. Eff.	76.8	Power Factor	80	Line-line Res. @ 25°C	20.283 Ω
Rating - Duty	40C	AMB-CONT	Temp. Rise @ Rated Load		17°C
S.F. Amps	2.8/1.4	Temp. Rise @ S.F. Load		21°C	
			Locked-rotor Power Factor	69	
			Rotor inertia	0.0148 LB-FT ²	

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	64	75	82	87	89	87
Efficiency	60.9	73.6	77.6	78.8	78.8	77.7	78.8
Speed	3558.7	3525.3	3490.1	3452.4	3410.2	3364.3	3410
Line amperes	0.661	0.769	0.92	1.1	1.3	1.54	1.3


ABB Motors and Mechanical Inc.

WINDING # 34WG719


Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 3450 RPM 460 V 3416M


TORQUES (LB-FT): PO=5.62 PU=3.98 LR=5.14 LRA=9.2



2/22/2024 ACPERF, record # 44882



CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005