

BALDOR • RELIANCE

Customer information packet

EM31159

1.5HP, 1170RPM, 3PH, 60HZ, 56H, 3540M, ODP, F1

Class - None

Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.

8/11/2024 5:06:35 AM

Specifications

Enclosure	ODP
Frame	56H
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.200 A @ 208.0 V 5.000 A @ 230.0 V 2.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	F

Part detail

Revision	F
Type	AC
Mech. spec.	35J382
Base	
Status	PRD/A
Elec. spec.	35WGG334
Layout	35LYJ382
Eff. date	05-16-2024
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	09-09-2022

Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3540M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	14.00 IN
Power Factor	66
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3155LUA									
CAT.NO.	EM31159								
SPEC.	35J382G334G1								
HP	1.5								
VOLTS	230/460								
AMPS	5/2.5								
RPM	1170								
FRAME	56H		HZ	60		PH	3		
SF	1.15	CODE	L	DES	B	CLASS	F		
F.L. AVG. EFF.	84	PF	66						
RATING	40C AMB-CONT								
CC									
DE	6205		ODE	6203					
ENCL	ODP	SN							
USABLE AT	N/A								

AC Induction Motor Performance Data

Record # 87765

Preliminary Data Sheet

Winding: 35WGG334-R002		Type: 3540M	Enclosure: OPEN	
Nameplate Data			460 V, 60 Hz: High Voltage Connection	
Rated Output (HP)	1.5	Full Load Torque	6.78 LB-FT	
Volts	230/460	Start Configuration	direct on line	
Full Load Amps	5/2.5	Breakdown Torque	24.05 LB-FT	
R.P.M.	1170	Pull-up Torque	13.05 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque	15.2 LB-FT
NEMA Design Code	B KVA Code	L	Starting Current	15.6 A
Service Factor (S.F.)	1.15	No-load Current	1.66 A	
NEMA Nom. Eff.	84 Power Factor	66	Line-line Res. @ 25°C	10.6 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	69°C	
S.F. Amps	5.6/2.8	Temp. Rise @ S.F. Load	82°C	
		Locked-rotor Power Factor	43.7	
		Rotor inertia	0.29 lb-ft ²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	45	57	66	72	75	70
Efficiency	72.7	81.1	83.6	83.7	82.9	81.1	83.2
Speed	1193	1186	1179	1171	1162	1152	1166
Line amperes	1.72	1.9	2.19	2.55	2.96	3.45	2.8


ABB Motors and Mechanical Inc.

WINDING # 35WGG334


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1170 RPM 460 V 3540M

TORQUES (LB-FT): PO=24.05 PU=13.05 LR=15.2 LRA=15.6



8/11/2024 ACPERF, record # 87765



CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS