

ABB BALDOR RELIANCE III

Customer information packet

EM3155T-G

2HP, 3450RPM, 3PH, 60HZ, 143T, 3524M, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	143T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.000 A @ 230.0 V 5.600 A @ 208.0 V 2.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	X
Type	AC
Mech. spec.	35Z948
Base	
Status	PRD/A
Elec. spec.	35WGQ054
Layout	35LYZ948
Eff. date	01-08-2026
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	11-17-2011

Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.62 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	EM3155T-G								
SPEC.	35Z948Q054G1								
HP	2								
VOLTS	230/460								
AMPS	5/2.5								
RPM	3450								
FRAME	143T		HZ	60			PH	3	
SF	1.15	CODE	K	DES	B	CLASS	H		
NEMA NOM. EFF	85.5	PF	87						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	SN							
DE	6205		ODE	6203					
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 2HP 190/380V 6/3A							SF1.0	

AC Induction Motor Performance Data

Record # 53133

Typical performance - not guaranteed values

Winding: 35WGQ054-R009			Type: 3524M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		2	Full Load Torque		3 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		5/2.5	Breakdown Torque		11 LB-FT		
R.P.M.		3450	Pull-up Torque		8 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		9.6 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		21.5 A
Service Factor (S.F.)		1.15		No-load Current		1 A	
NEMA Nom. Eff.		85.5	Power Factor	87	Line-line Res. @ 25°C		7.37 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		31°C	
S.F. Amps				Temp. Rise @ S.F. Load		37°C	
				Locked-rotor Power Factor		53.6	
				Rotor inertia		0.0657 LB-FT2	

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	51	70	81	86	87	88	87
Efficiency	78.3	85.2	86.9	86.5	85.6	84.2	86
Speed	3570	3541	3510	3476	3441	3403	3455
Line amperes	1.2	1.6	2	2.5	3.1	3.7	2.86

ABB Motors and Mechanical Inc.

WINDING # 35WGQ054

Typical performance - not guaranteed values.

2 HP 3 PH 60 HZ 3450 RPM 460 V 3524M

TORQUES (LB-FT) : PO=11 PU=8 LR=9.6 LRA=21.5





