

ABB BALDOR RELIANCE III

Customer information packet

EM3207T-G

1.5HP, 1170RPM, 3PH, 60HZ, 182T, 3628M, OPSB, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	182T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.000 A @ 230.0 V 5.100 A @ 208.0 V 2.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	Q
Type	AC
Mech. spec.	36M526
Base	
Status	PRD/A
Elec. spec.	36WGS949
Layout	36LYM526
Eff. date	03-13-2026
CD Diagram	CD0005
Poles	06
Leads	9#16
Proprietary	False
Created date	07-03-2012

Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3628M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.00 IN
Power Factor	64
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP1259L											
CAT.NO.	EM3207T-G										
SPEC.	36M526S949G1										
HP	1.5										
VOLTS	230/460										
AMP	5/2.5										
RPM	1170										
FRAME	182T		HZ	60				PH	3		
SER.F.	1.15	CODE	K	DES	B	CL	H				
NEMA-NOM-EFF	86.5	PF	64								
RATING	40C AMB-CONT										
CC	010A										
DE	6206		ODE	6205							
ENCL	OPSB	SN									

AC Induction Motor Performance Data

Record # 39006

Typical performance - not guaranteed values

Winding: 36WGS949-R002			Type: 3628M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1.5	Full Load Torque		6.72 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		5/2.5	Breakdown Torque		22 LB-FT		
R.P.M.		1170	Pull-up Torque		13.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		15.4 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		15.8 A
Service Factor (S.F.)		1.15	No-load Current		1.65 A		
NEMA Nom. Eff.		86.5	Power Factor	64	Line-line Res. @ 25°C		8.0884 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		24°C
S.F. Amps			Temp. Rise @ S.F. Load		28°C		

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	43	55	64	69	73	67
Efficiency	75.7	84.3	86.6	87	86.5	85.4	86.7
Speed	1192.8	1185.9	1178.5	1170.6	1161.7	1151.4	1165
Line amperes	1.72	1.91	2.18	2.52	2.94	3.39	2.77


ABB Motors and Mechanical Inc.


WINDING # 36WGS949

Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1170 RPM 460 V 3628M

TORQUES (LB-FT): PO=22 PU=13.4 LR=15.4 LRA=15.8





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005