

ABB BALDOR RELIANCE III

Customer information packet

EM3311T-58

7.5HP, 1460RPM, 3PH, 50HZ, 213T, 3736M, OPSB, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	400.0 V @ 50 HZ
Agency Approvals	CE CURUS IE3 UKCA WEEE C U R U S
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.800 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	J
Type	AC
Mech. spec.	37B101
Base	
Status	PRD/A
Elec. spec.	37WGS060
Layout	37LYB101
Eff. date	11-08-2024
CD Diagram	CD0382
Poles	04
Leads	6#14
Proprietary	False
Created date	12-22-2015

Heater Indicator	No Heater
High Voltage Full Load Amps	10.8 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3736M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.45 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1460 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2716L									
CAT NO	EM3311T-58								
SPEC.	37B101S060G1								
HP	7.5/5.5KW					PH	3		
VOLTS	400								
AMP	10.8								
R.P.M. (1/MIN)	1460								
FRAME	213T		HZ	50		I.P.		23	
SER.F.	1.15	CODE	H	DES	B	CL	F		
NOM.EFF.	89.6		% (100%)						
PF	82								
RATING	40C AMB-S1 CONT				CC				
DE BRG	6307		ODE	6206					
ENCL	OPSB	SN							
BLANK	IE3-90.7(75%)90.6(50%)								
	IC01 58KG								

