ABB BALDOR RELIANCE

Customer information packet

EM3313T-G

10HP, 1768RPM, 3PH, 60HZ, 215T, 3738M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 4:00:25 PM

Specifications

Enclosure	OPSB
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	28.000 A @ 208.0 V
	25.400 A @ 230.0 V
	12.700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.7 a

Part Detail

Revision	A
Type	AC
Mech. spec.	37J839
Base	
Status	PRD/A
Elec. spec.	37WGZ710
Layout	37LYJ839
Eff. date	01-08-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-07-2025

Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.45 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1768 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA										
CAT.NO.	EM3313T-G									
SPEC.	37J839Z710G1									
HP	10									
VOLTS	230/460									
AMPS	25.4/12.7									
RPM	1768									
FRAME	215T	**HZ**	60			**PH**	3			
SF	1.15	**CODE**	H	**DES**	B	**CLASS**	H			
NEMA NOM. EFF	91.7	**PF**	81							
RATING	40C AMB-CONT									
CC	010A									
ENCL	OPSB	**SN**								
DE	6307	**ODE**	6206							
VPWM INVERTER READY	SFA 28.8/14.4									
CT30-60(2:1) VT3-60(20:1)										
USABLE AT	50HZ 7.5HP 190/380V 23.4/11.7A									SF1.0

AC Induction Motor Performance Data
Record # 115744
Typical performance - not guaranteed values

Winding: 37WGZ710-R001	**Type:** 3738M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.77 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25.4/12.7	**Breakdown Torque**	108 LB-FT
R.P.M.			1768	**Pull-up Torque**	40.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	52.3 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	87.6 A
Service Factor (S.F.)			1.15	**No-load Current**	5.88 A
NEMA Nom. Eff.	91.7	**Power Factor**	81	**Line-line Res. @ 25ºC**	1.1433 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	40°C
S.F. Amps			28.8/14.4	**Temp. Rise @ S.F. Load**	50°C
				Locked-rotor Power Factor	37.2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	40	62	74	79	82	83	81
Efficiency	88	91.9	92.3	91.7	90.7	89.3	91.1
Speed	1792.7	1785.4	1777.2	1768.4	1757.8	1747.3	1762
Line amperes	6.58	8.16	10.3	12.9	15.8	18.9	14.6


ABB Motors and Mechanical Inc.


WINDING # 37WGZ710

10 HP 3 PH 60 HZ 1768 RPM 460 V 3738M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=108 PU=40.7 LR=52.3 LRA=87.6





37LYJ839
(717-735) = 16.32
(736-744) = 17.45
(745-750) = 18.20
(751-756) = 18.95
3.44
3.88
3.38
GREASE FITTING
(OR OPTIONAL PLUG)
(EA. END)
NAMEPLATE
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
Ø9.57
7.90
LIFTING LUG
(1 EA. END)
10.04
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.73
4.75
9.50
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: B
VERSION: 02
REVISED: 11:26:35 10/11/2022
TDR: 000001197758
MODEL NO. 37LYJ839
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HOR 213-5T OPSB M, AEGIS INT SHAFT GND
37LYJ839

CD0005







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS