

ABB BALDOR RELIANCE III

Customer information packet

EM3545-G

1HP, 3450RPM, 3PH, 60HZ, 56, 3516M, TEFC, F1, N

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.800 A @ 230.0 V 3.000 A @ 208.0 V 1.400 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	X
Type	AC
Mech. spec.	35Z951
Base	
Status	PRD/A
Elec. spec.	35WGY474
Layout	35LYZ951
Eff. date	01-05-2026
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	11-18-2011

Heater Indicator	No Heater
High Voltage Full Load Amps	1.4 a
Insulation Class	H
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3516M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.23 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EM3545-G								
SPEC	35Z951Y474G1								
HP	1								
VOLTS	230/460								
AMPS	2.8/1.4								
RPM	3450								
FRAME	56		HZ	60		PH	3		
SF	1.25	CODE	K	DES	B	CLASS	H		
NEMA NOM. EFF	77	PF	87						
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6205	ODE	6203						
VPWM INVERTER READY	SFA 3.4/1.7								
CT6-60H(10:1)VT3-60H(20:1									
	50Hz 1HP 190/380V 3.4/1.7A							SF1.0	

AC Induction Motor Performance Data

Record # 36063

Typical performance - not guaranteed values

Winding: 35WGY474-R015			Type: 3516M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1	Full Load Torque		1.5 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		2.8/1.4	Breakdown Torque		5.6 LB-FT		
R.P.M.		3450	Pull-up Torque		3.91 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		4.01 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		8.99 A
Service Factor (S.F.)		1.25	No-load Current		0.66 A		
NEMA Nom. Eff.		77	Power Factor	87	Line-line Res. @ 25°C		19.4 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		47°C
S.F. Amps		3.4/1.7	Temp. Rise @ S.F. Load		60°C		
			Locked-rotor Power Factor		64		
			Rotor inertia		0.0443 LB-FT2		

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	57	74	82	85	87	87	87
Efficiency	53.9	67.9	73.4	75.1	75.6	74.5	75.6
Speed	3549	3513	3473	3431	3383	3329	3383
Line amperes	0.769	0.939	1.17	1.43	1.72	2.06	1.72


ABB Motors and Mechanical Inc.


WINDING # 35WGY474

Typical performance - not guaranteed values.




1 HP 3 PH 60 HZ 3450 RPM 460 V 3516M

TORQUES (LB-FT) : PO=5.6 PU=3.91 LR=4.01 LRA=8.99





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005