

ABB BALDOR RELIANCE III

Customer information packet

EM3218TA

5HP, 1750RPM, 3PH, 60HZ, 184T, 3640M, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.000 A @ 208.0 V 6.600 A @ 460.0 V 13.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	N
Type	AC
Mech. spec.	36H827
Base	
Status	PRD/A
Elec. spec.	36WGS536
Layout	36LYH827
Eff. date	03-30-2026
CD Diagram	CD0007
Poles	04
Leads	12#16
Proprietary	False
Created date	11-12-2010

Heater Indicator	No Heater
High Voltage Full Load Amps	6.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	12 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3640M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.17 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload



Winding Thermal 1 Location	KO
Winding Thermal 2	None

Nameplate

NP2601L											
CAT.NO.	EM3218TA										
SPEC.	36H827S536G1										
HP	5										
VOLTS	230/460										
AMP	13.2/6.6										
RPM	1750										
FRAME	184T		HZ	60				PH	3		
SER.F.	1.15	CODE	J	DES	B	CL	F				
NEMA-NOM-EFF	89.5	PF	80								
RATING	40C AMB-CONT										
CC	010A										
DE	6206		ODE	6205							
ENCL	OPSB	SN									

AC Induction Motor Performance Data

Record # 32558

Typical performance - not guaranteed values

Winding: 36WGS536-R005			Type: 3640M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		5	Full Load Torque		15 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		13.2/6.6	Breakdown Torque		44.8 LB-FT		
R.P.M.		1750	Pull-up Torque		25.5 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		30.1 LB-FT	
NEMA Design Code		B	KVA Code	J	Starting Current		44.8 A
Service Factor (S.F.)		1.15		No-load Current		2.97 A	
NEMA Nom. Eff.		89.5	Power Factor	80	Line-line Res. @ 25°C		2.62 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		44°C	
S.F. Amps				Temp. Rise @ S.F. Load		54°C	
				Locked-rotor Power Factor		41	
				Rotor inertia		0.372 LB-FT2	

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	42	63	75	80	83	84	82
Efficiency	85.4	89.8	90.2	89.6	88.5	86.5	88.9
Speed	1789	1779	1767	1754	1740	1722	1746
Line amperes	3.32	4.13	5.25	6.57	8.03	9.65	7.45


ABB Motors and Mechanical Inc.

WINDING # 36WGS536

Typical performance - not guaranteed values.


5 HP 3 PH 60 HZ 1750 RPM 460 V 3640M

TORQUES (LB-FT) : PO=44.8 PU=25.5 LR=30.1 LRA=44.8






CD0007




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED "CK" PLANT CODE

REV. LTR: E

BY: EAH

REVISED: 05/06/99 17:1

TDR: 0181040

200000

FILE: AAA00008370

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, DV, THERMAL, 12 LEADS

CD0007