

ABB BALDOR RELIANCE III

Customer information packet

EM3309T-BG

5HP, 1160RPM, 3PH, 60HZ, 215T, 3744M, OPSB, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.400 A @ 460.0 V 14.800 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	P
Type	AC
Mech. spec.	37N346
Base	
Status	PRD/A
Elec. spec.	37WGS521
Layout	37LYN346
Eff. date	05-11-2026
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	10-28-2013

High Voltage Full Load Amps	7.4 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3744M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	17.45 IN
Power Factor	71
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1160 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	EM3309T-BG								
SPEC.	37N346S521G1								
HP	5								
VOLTS	230/460								
AMPS	14.8/7.4								
RPM	1160								
FRAME	215T		HZ	60		PH	3		
SF	1.15	CODE	K	DES	A	CLASS	H		
NEMA NOM. EFF	89.5	PF	71						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	SN							
DE	6307		ODE	6206					
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50Hz 5HP 190/380V 17.2/8.6A						SF1.0		

AC Induction Motor Performance Data

Record # 62644

Typical performance - not guaranteed values

Winding: 37WGS521-R002			Type: 3744M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		5	Full Load Torque		22.5 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		14.8/7.4	Breakdown Torque		77.9 LB-FT		
R.P.M.		1160	Pull-up Torque		47.4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		54.8 LB-FT	
NEMA Design Code		A	KVA Code	K	Starting Current		53 A
Service Factor (S.F.)		1.15	No-load Current		3.84 A		
NEMA Nom. Eff.		89.5	Power Factor	71	Line-line Res. @ 25°C		1.74 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		33°C
S.F. Amps					Temp. Rise @ S.F. Load		40°C
					Locked-rotor Power Factor		22.7
					Rotor inertia		1.09 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	53	65	71	75	76	73
Efficiency	84.7	89.4	89.7	89.7	88.5	86.5	89
Speed	1192	1184	1174	1165	1154	1139	1158
Line amperes	4.14	4.95	6.08	7.36	8.92	10.7	8.3


ABB Motors and Mechanical Inc.


WINDING # 37WGS521

Typical performance - not guaranteed values.




5 HP 3 PH 60 HZ 1160 RPM 460 V 3744M

TORQUES (LB-FT): PO=77.9 PU=47.4 LR=54.8 LRA=53





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005