ABB BALDOR RELIANCE

Customer information packet

EM3554T-57

1.5/1.1KWHP, 1470RPM, 3PH, 50HZ, 145T, 3524M
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 11:17:42 AM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	400.0 V @ 50 HZ
	230.0 V @ 50 HZ
Agency Approvals	C UR US
	CE
	CURUS
	IE3
	UKCA
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.500 A @ 230.0 V
	2.600 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	D
Type	AC
Mech. spec.	35AA001
Base	
Status	PRD/A
Elec. spec.	35WGG296
Layout	35LYAA001
Eff. date	10-28-2025
CD Diagram	CD0022
Poles	04
Leads	6#18 Y
Proprietary	False
Created date	03-11-2022

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.6 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3524M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.31 IN
Power Factor	73
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1470 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP2716L									
CAT NO	EM3554T-57								
SPEC.	35AA001G296G1								
HP	1.5/1.1KW				**PH**	3			
VOLTS	230/400								
AMP	4.5/2.6								
R.P.M. (1/MIN)	1470								
FRAME	145T	**HZ**	50			**I.P.**	44		
SER.F.	1.15	**CODE**	L	**DES**	B	**CL**	F		
NOM.EFF.	84.2		**% (100%)**						
PF	73								
RATING	40C AMB-S1 CONT			**CC**					
DE BRG	6205		**ODE**	6203					
ENCL	TEFC	**SN**							
BLANK	SFA 4.8/2.8								
	IC411 19KG								

AC Induction Motor Performance Data
Record # 86992
Preliminary Data Sheet

Winding: 35WGG296-R001	**Type:** 3524M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			1.5
Volts			230/400
Full Load Amps			4.5/2.6
R.P.M.			1470
Hz	50	**Phase**	3
NEMA Design Code	B	**KVA Code**	L
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	84.2	**Power Factor**	73
Rating - Duty			40C AMB-CONT
S.F. Amps			5/2.9

400 V, 50 Hz: High Voltage Connection	
Full Load Torque	5.39 LB-FT
Start Configuration	direct on line
Breakdown Torque	18.9 LB-FT
Pull-up Torque	10.8 LB-FT
Locked-rotor Torque	13.3 LB-FT
Starting Current	20 A
No-load Current	1.69 A
Line-line Res. @ 25ºC	12.6 Ω
Temp. Rise @ Rated Load	56°C
Temp. Rise @ S.F. Load	67°C
Locked-rotor Power Factor	70
Rotor inertia	0.173 lb-ft²

Load Characteristics 400 V, 50 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	51	64	73	79	83	80
Efficiency	72.7	81.7	84	84.3	83.2	81.7	84.2
Speed	1492	1486	1478	1470	1460	1450	1462
Line amperes	1.75	1.94	2.25	2.61	3.07	3.58	2.75


ABB Motors and Mechanical Inc.


WINDING # 35WGG296

1.5 HP 3 PH 50 HZ 1470 RPM 400 V 3524M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=18.9 PU=10.8 LR=13.3 LRA=20





35LYAA001
510-520 = 12.28
521-528 = 13.28
529-535 = 14.16
536-546 = 15.53
3.75
2.50
2.25
GREASE FITTING
(EACH END)
NAMEPLATE
Ø7.19
.19 KEY
1.38 LONG
Ø .8750
.8745
4.00
2.25
5.00
.50
5.94
6 HOLES
.38 DIA.
6.61
5.71
4.55
6.78
3.50
3.44
THERMAL
(WHEN
REQ'D)
LEAD HOLE
1.09 DIA.
2.75
2.75
4.59
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: F
VERSION: 06
REVISED: 12:55:25 03/10/2023
TDR: 000001205626
MODEL NO. 35LYAA001
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 143-5T TEFC 35M W/1.09 LEAD HOLE
35LYAA001

CD0022







NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: –
		MTL: –	3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022