ABB BALDOR RELIANCE

Customer information packet

EM3558T-8

2HP, 1765RPM, 3PH, 60HZ, 145T, 3528M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/7/2026 11:11:39 AM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.700 A @ 200.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.7 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE

Part Detail

Revision	G
Type	AC
Mech. spec.	35A001
Base	
Status	PRD/A
Elec. spec.	35WGG112
Layout	35LYA001
Eff. date	02-26-2025
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	03-11-2022

KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.31 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L											
CAT.NO.	EM3558T-8										
SPEC.	35A001G112G1										
HP	2										
VOLTS	200										
AMP	6.7										
RPM	1765										
FRAME	145T	**HZ**	60	**PH**	3						
SER.F.	1.15	**CODE**	K	**DES**	B	**CL**	F				
NEMA-NOM-EFF	86.5	**PF**	82								
RATING	40C AMB-CONT										
CC	010A										
DE	6205	**ODE**	6203								
ENCL	TEFC	**SN**									
VPWM INVERTER READY											
CT6-60H(10:1)VT3-60H(20:1											
	SFA 7.28										

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data
Record # 81991
Typical performance - not guaranteed values

Winding: 35WGG112-R003	**Type:** 3526M	**Enclosure:** TEFC

Nameplate Data				**200 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			2	**Full Load Torque**	5.95 LB-FT
Volts			200	**Start Configuration**	direct on line
Full Load Amps			6	**Breakdown Torque**	23.11 LB-FT
R.P.M.			1755	**Pull-up Torque**	14 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	16.93 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	55.76 A
Service Factor (S.F.)			1.15	**No-load Current**	3.84 A
NEMA Nom. Eff.	86.5	**Power Factor**	82	**Line-line Res. @ 25ºC**	1.86 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	69°C
				Locked-rotor Power Factor	56.9
				Rotor inertia	0.188 lb-ft²

Load Characteristics 200 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	55	69	77	81	84	79
Efficiency	77.5	85	86.7	86.4	85.1	83.5	85.6
Speed	1791	1783	1774	1765	1756	1744	1760
Line amperes	4.03	4.6	5.44	6.5	7.8	9.13	7.28

ABB Motors and Mechanical Inc.

WINDING # 35WGG112

2 HP 3 PH 60 HZ 1755 RPM 200 V 3526M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=23.11 PU=14 LR=16.93 LRA=55.76



9/7/2026 ACPERF, record # 81991


35LYA001
510-520 = 12.29 [312.16]
521-528 = 13.29 [337.57]
529-535 = 14.17 [359.92]
536-546 = 15.54 [394.72]
[63.50] 2.50
[95.37] 3.75
GREASE FITTINGS EACH END
[57.15] 2.25
[182.67] Ø7.19
NAMEPLATE
.19 KEY 1.38 LONG
[22.23] [22.21] Ø.8750 Ø.8745
6 HOLES Ø.38
[101.60] 4.00
[57.15] 2.25
[127] 5.00
[12.70] .50
[150.88] 5.94
[167.94] 6.61
[146.03] 5.75
4.55
[172.21] 6.78
[88.90] [87.38] 3.50 3.44
THERMAL WHEN (REQ'D)
LEAD HOLE Ø.88
[69.85] 2.75
[69.85] 2.75
[117.60] 4.63
[82.55] 3.25
[165.10] 6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: AB
VERSION: 10
REVISED: 10:15:21 04/06/2023
TDR: 000001205626
MODEL NO. 35LYA001
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 143-5T TEFC 35M
SH 1 of 1
35LYA001

CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1